

TYANA MH Heavy duty flat delivery hose



Inner diameter		Working pressure		Burst pressure		Weight	Length
In	mm	bar	psi	bar	psi	g/m	m
2	52	16	232	48	696	470	50/100
2 1/2	64	15.0	218	45	653	780	50/100
3	76	12.0	174	36.0	522	800	50/100
-	90	11.0	160	33.0	479	1015	50/100
4	102	11	160	32	464	1115	50/100
6	153	6	87	18	261	1680	50/100
8	203	5	73	15	218	2700	50/100

Construction

- Flexible PVC/NBR lining
- High tensile synthetic textile reinforcement
- Light chemical and weather resistant PVC outer cover

Temperature range

- -10°C to +60°C
- (-14°F to +140°F)

Application

- Heavy duty discharge of water, light chemicals and other liquids in construction, agriculture and industry