

| PW9130i1000T-XL | | | | | |
|------------------------|------|-------|-------|-------|-------|
| 1000/900 | 6.1 | 31.5 | 51.4 | 82.0 | 100.3 |
| 750/675 | 9.2 | 42.9 | 80.2 | 108.1 | 158.3 |
| 500/450 | 19.1 | 68.2 | 110.8 | 192.6 | 246.2 |
| 250/225 | 30.5 | 123.6 | 271.5 | 368.0 | 482.7 |

| PW9130i2000T-XL | | | | | |
|------------------------|------|-------|-------|-------|-------|
| 2000/1800 | 11.2 | 44.3 | 79.0 | 115.0 | 161.8 |
| 1500/1350 | 17.0 | 60.0 | 112.0 | 164.0 | 203.0 |
| 1000/900 | 27.9 | 95.8 | 168.0 | 258.0 | 336.0 |
| 500/450 | 54.9 | 169.0 | 336.0 | 490.0 | 608.0 |

| PW9130i3000T-XL | | | | | |
|------------------------|------|-------|-------|-------|-------|
| 3000/2700 | 6.4 | 21.3 | 51.5 | 66.0 | 93.5 |
| 2250/2025 | 8.6 | 37.6 | 67.0 | 101.8 | 128.0 |
| 1500/1350 | 15.6 | 60.0 | 100.0 | 169.0 | 215.0 |
| 750/675 | 40.0 | 139.0 | 226.0 | 311.0 | 444.0 |