

# Eaton 93E UPS Selection Guide



## Table of Contents

Eaton 93E 15-80 kVA .....	2
Eaton 93E 100-200 kVA.....	3



Powering Business Worldwide

## Eaton 93E 15-80 kVA

Power rating [kVA], PF 0.9	Runtime [min]	Reference	Description	Details
15	0	93E15KMBSB	93E 15kVA	includes battery accessories, MBS*
15	4	93E15KMBSBI-1	93E 15kVA 1x9Ah	Includes 1 x 32 batteries, MBS*
15	11	93E15KMBSBI	93E 15kVA 2x9Ah	Includes 2 x 32 batteries, MBS*
20	0	93E20KMBSB	93E 20kVA	includes battery accessories, MBS*
20	8	93E20KMBSBI	93E 20kVA 2x9Ah	Includes 2 x 32 batteries, MBS*
30	0	93E30KMBSB	93E 30kVA	includes battery accessories, MBS*
30	8	93E30KMBSBI	93E 30kVA 3x9Ah	Includes 3 x 32 batteries, MBS*
40	0	93E40KMBSB	93E 40kVA	includes battery accessories, MBS*
40	8	93E40KMBSBI	93E 40kVA 4x9Ah	Includes 4 x 32 batteries, MBS*
60	0	93E60KMBSN	93E 60kVA	MBS*
80	0	93E80KMBSN	93E 80kVA	MBS*

\* Maintenance Bypass Switch



Powering Business Worldwide

## Eaton 93E 100-200 kVA

Power rating [kVA], PF 0.9	Reference	Description	Details
100	93E100K	93E-100kVA	
100	93E100KMBS	93E-100kVA-MBS	MBS*
120	93E120K	93E-120kVA	
120	93E120KMBS	93E-120kVA-MBS	MBS*
160	93E160K	93E-160kVA	
200	93E200K	93E-200kVA	

\* Maintenance Bypass Switch