

Which UPS?













Your at-a-glance guide to Eaton UPSs.



Powering Business Worldwide

For more information visit our
online selection tool

www.eaton.eu/selectors

	Application	Software	Power rating	UPS format	Product description	Part number	Standard warranty	Communication	Outlet	Product dimensions and weight (h x w x d mm/kg)			
PC, Workstation and Home UPS	PC, Workstation and Home UPS												
		Eaton Ellipse ECO		EUC	500VA/300W	Tower (Rack option)	Ellipse ECO 500	EL500IEC	2 years	–	IEC 4 (3+1)	263 x 81 x 235 / 2.9	
		EUC	650VA/400W	Tower (Rack option)	Ellipse ECO 650	EL650IEC	2 years	–	IEC 4 (3+1)	263 x 81 x 235 / 3.6			
		EUC	650VA/400W	Tower (Rack option)	Ellipse ECO 650 USB	EL650USBIEC	2 years	USB	IEC 4 (3+1)	263 x 81 x 235 / 3.6			
		EUC	800VA/500W	Tower (Rack option)	Ellipse ECO 800 USB	EL800USBIEC	2 years	USB	IEC 4 (3+1)	263 x 81 x 235 / 4.1			
		EUC	1200VA/750W	Tower (Rack option)	Ellipse ECO 1200 USB	EL1200USBIEC	2 years	USB	IEC 8 (4+4)	305 x 81 x 312 / 6.7			
		EUC	1600VA/1000W	Tower (Rack option)	Ellipse ECO 1600 USB	EL1600USBIEC	2 years	USB	IEC 8 (4+4)	305 x 81 x 312 / 7.8			
		Eaton Ellipse PRO		EUC	650VA/400W	Tower (Rack option)	Ellipse PRO 650	ELP650IEC	3 years	USB	IEC 4 (3+1)	206 x 82 x 285 / 6.6	
		EUC	850VA/510W	Tower (Rack option)	Ellipse PRO 850	ELP850IEC	3 years	USB	IEC 4 (3+1)	206 x 82 x 285 / 7.3			
		EUC	1200VA/750W	Tower (Rack option)	Ellipse PRO 1200	ELP1200IEC	3 years	USB	IEC 8 (4+4)	275 x 82 x 390 / 9.9			
		EUC	1600VA/1000W	Tower (Rack option)	Ellipse PRO 1600	ELP1600IEC	3 years	USB	IEC 8 (4+4)	275 x 82 x 390 / 11.3			
		Network and Server UPS											
			Eaton 55C		IPS	500VA/350W	Tower	55C 500	55C500i	2 years	USB/Serial	IEC 4	210 x 150 x 240 / 6.6
	IPS		750VA/525W	Tower	55C 750	55C750i	2 years	USB/Serial	IEC 6	210 x 150 x 340 / 10.4			
IPS	1000VA/700W		Tower	55C 1000	55C1000i	2 years	USB/Serial	IEC 8	210 x 150 x 340 / 11.1				
IPS	1500VA/1050W		Tower	55C 1500	55C1500i	2 years	USB/Serial	IEC 8	210 x 150 x 410 / 15.2				
	Eaton 5P		IPS	650VA/420W	Tower	5P 650	5P650i	3 years*	USB/Serial/Slot	IEC 4/2 Controlled	230 x 150 x 345 / 7.8		
	IPS		850VA/600W	Tower	5P 850	5P850i	3 years*	USB/Serial/Slot	IEC 6/3 Controlled	230 x 150 x 345 / 10.4			
	IPS		1150VA/770W	Tower	5P 1150	5P1150i	3 years*	USB/Serial/Slot	IEC 8/4 Controlled	230 x 150 x 345 / 11.1			
	IPS		1550VA/1100W	Tower	5P 1550	5P1550i	3 years*	USB/Serial/Slot	IEC 8/4 Controlled	230 x 150 x 445 / 15.6			
	IPS		650VA/420W	Rack	5P 650	5P650iR	3 years*	USB/Serial/Slot	IEC 4/2 Controlled	43.2(1U) x 438 x 364 / 8.6			
	IPS		850VA/600W	Rack	5P 850	5P850iR	3 years*	USB/Serial/Slot	IEC 4/2 Controlled	43.2(1U) x 438 x 509 / 13.8			
	IPS		1150VA/770W	Rack	5P 1150	5P1150iR	3 years*	USB/Serial/Slot	IEC 6/3 Controlled	43.2(1U) x 438 x 509 / 14.6			
	IPS		1550VA/1100W	Rack	5P 1550	5P1550iR	3 years*	USB/Serial/Slot	IEC 6/3 Controlled	43.2(1U) x 438 x 554 / 19.4			
			Eaton 5PX		IPS	1500VA/1350W	Rack/Tower convertible	5PX 1500 RT 2U	5PX1500iRT	3 years*	USB/Serial/Slot	8IEC/4 Controlled	441 x 86.2 x 522 / 27.6
			IPS	1500VA/1350W	Rack/Tower convertible	5PX 1500 RT 2U Netpack	5PX1500iRTN	3 years*	USB/Serial/Network-MS card	8IEC/4 Controlled	441 x 86.2 x 522 / 27.6		
IPS		2200VA/1980W	Rack/Tower convertible	5PX 2200 RT 2U	5PX2200iRT	3 years*	USB/Serial/Slot	9IEC/4 Controlled	441 x 86.2 x 522 / 28.5				
IPS		2200VA/1980W	Rack/Tower convertible	5PX 2200 RT 2U Netpack	5PX2200iRTN	3 years*	USB/Serial/Network-MS card	9IEC/4 Controlled	441 x 86.2 x 522 / 28.5				
IPS		3000VA/2700W	Rack/Tower convertible	5PX 3000 RT 3U	5PX3000iRT3U	3 years*	USB/Serial/Slot	9IEC/4 Controlled	441 x 130.7 x 497 / 37.33				
IPS		3000VA/2700W	Rack/Tower convertible	5PX 3000 RT 2U Netpack	5PX3000iRTN	3 years*	USB/Serial/Network-MS card	9IEC/4 Controlled	441 x 86.2 x 647 / 38.08				
	Eaton EX		IPS	700VA/630W	Tower	Eaton EX 700	68 180	2 years	USB/Serial/Slot	6 IEC/3 Controlled	242 x 158 x 400 / 12.5		
	IPS	1000VA/900W	Tower	Eaton EX 1000	68 181	2 years	USB/Serial/Slot	6 IEC/3 Controlled	242 x 158 x 400 / 15				
	IPS	1500VA/1350W	Tower	Eaton EX 1500	68 183	2 years	USB/Serial/Slot	6 IEC/3 Controlled	242 x 158 x 450 / 18				
		Eaton 9130		IPS	700VA/630W	Tower	9130 700 Tower	103006433-6591	2 years	USB/Serial/Slot	6 IEC 10A	230 x 160 x 350 / 12.2	
		IPS	1000VA/900W	Tower	9130 1000 Tower XL	103006434-6591	2 years	USB/Serial/Slot	6 IEC 10A	230 x 160 x 380/14,5			
		IPS	1500VA/1350W	Tower	9130 1500 Tower XL	103006435-6591	2 years	USB/Serial/Slot	6 IEC 10A	230 x 160 x 430/19			
		IPS	2000VA/1800W	Tower	9130 2000 Tower XL	103006436-6591	2 years	USB/Serial/Slot	8 IEC 10A/1 IEC 16A	325 x 214 x 410 / 34.5			
		IPS	3000VA/2700W	Tower	9130 3000 Tower XL	103006437-6591	2 years	USB/Serial/Slot	8 IEC 10A/1 IEC 16A	325 x 214 x 410 / 34.5			
		IPS	5000VA/4500W	Tower	9130 5000 Tower XL	103007841-6591	2 years	USB/Serial/Slot	Hardwired	574 x 244 x 542 / 75.5			
		IPS	6000VA/5400W	Tower	9130 6000 Tower XL	103007842-6591	2 years	USB/Serial/Slot	Hardwired	574 x 244 x 542 / 75.5			
		IPS	1000VA/900W	Rack	9130 1000 Rack XL 2U	103006455-6591	2 years	USB/Serial/Slot	6 IEC 10A	86.5 x 438 x 450 / 16			
		IPS	1500VA/1350W	Rack	9130 1500 Rack XL 2U	103006456-6591	2 years	USB/Serial/Slot	6 IEC 10A	86.5 x 438 x 450 / 19			
		IPS	2000VA/1800W	Rack	9130 2000 Rack XL 2U	103006457-6591	2 years	USB/Serial/Slot	8 IEC 10A/1 IEC 16A	86.5 x 438 x 600 / 29			
	IPS	3000VA/2700W	Rack	9130 3000 Rack XL 2U	103006463-6591	2 years	USB/Serial/Slot	8 IEC 10A/1 IEC 16A	86.5 x 438 x 600 / 29.5				
	Eaton 9PX 1:1		IPS	1000VA/1000W	Rack/Tower convertible	Eaton 9PX 1000i RT2U	9PX1000iRT2U	3 years*	USB/Serial/Slot	8 IEC 10A/ 4 controlled	86.5 x 440 x 450 / 17.5		
	IPS	1000VA/1000W	Rack/Tower convertible	Eaton 9PX 1000i RT2U Netpack	9PX1000iRTN	3 years*	USB/Serial/Network-MS	8 IEC 10A/ 4 controlled	86.5 x 440 x 450 / 17.5				
	IPS	1500VA/1500W	Rack/Tower convertible	Eaton 9PX 1500i RT2U	9PX1500iRT2U	3 years*	USB/Serial/Slot	8 IEC 10A/ 4 controlled	86.5 x 440 x 450 / 19				
	IPS	1500VA/1500W	Rack/Tower convertible	Eaton 9PX 1500i RT2U Netpack	9PX1500iRTN	3 years*	USB/Serial/Network-MS	8 IEC 10A/ 4 controlled	86.5 x 440 x 450 / 19				
	IPS	2200VA/2200W	Rack/Tower convertible	Eaton 9PX 2200i RT3U	9PX2200iRT3U	3 years*	USB/Serial/Slot	8 IEC 10A/ 2 IEC 16A / 5 controlled	130 x 440 x 485 / 24.5				
	IPS	2200VA/2200W	Rack/Tower convertible	Eaton 9PX 2200i RT2U	9PX2200iRT2U	3 years*	USB/Serial/Slot	8 IEC 10A/ 2 IEC 16A / 5 controlled	86.5 x 440 x 605 / 24.5				
	IPS	2200VA/2200W	Rack/Tower convertible	Eaton 9PX 2200i RT3U HotSwap IEC	9PX2200iRTBP	3 years*	USB/Serial/Slot	6 IEC 10A + 1 IEC 16A	130 x 440 x 485 / 24.5				
	IPS	2200VA/2200W	Rack/Tower convertible	Eaton 9PX 2200i RT3U HotSwap HW	9PX2200iRTBPH	3 years*	USB/Serial/Slot	Hardwired	130 x 440 x 485 / 24.5				
	IPS	2200VA/2200W	Rack/Tower convertible	Eaton 9PX 2200i RT2U Netpack	9PX2200iRTN	3 years*	USB/Serial/Network-MS	8 IEC 10A/ 2 IEC 16A / 5 controlled	86.5 x 440 x 605 / 24.5				
	IPS	3000VA/3000W	Rack/Tower convertible	Eaton 9PX 3000i RT3U	9PX3000iRT3U	3 years*	USB/Serial/Slot	8 IEC 10A/ 2 IEC 16A / 5 controlled	130 x 440 x 485 / 27.5				
	IPS	3000VA/3000W	Rack/Tower convertible	Eaton 9PX 3000i RT2U	9PX3000iRT2U	3 years*	USB/Serial/Slot	8 IEC 10A/ 2 IEC 16A / 5 controlled	86.5 x 440 x 605 / 27.5				
	IPS	3000VA/3000W	Rack/Tower convertible	Eaton 9PX 3000i RT3U HotSwap IEC	9PX3000iRTBP	3 years*	USB/Serial/Slot	6 IEC 10A + 1 IEC 16A	130 x 440 x 485 / 27.5				
	IPS	3000VA/3000W	Rack/Tower convertible	Eaton 9PX 3000i RT3U HotSwap HW	9PX3000iRTBPH	3 years*	USB/Serial/Slot	Hardwired	130 x 440 x 485 / 27.5				
	IPS	3000VA/3000W	Rack/Tower convertible	Eaton 9PX 3000i RT2U Netpack	9PX3000iRTN	3 years*	USB/Serial/Network-MS	8 IEC 10A/ 2 IEC 16A / 5 controlled	86.5 x 440 x 605 / 27.5				
	IPS	5000VA/4500W	Tower (Rack option)	Eaton 9PX 5000i HotSwap	9PX5KiBP	2 years	USB/Serial/Slot	3 IEC 10A + 2 IEC 16A + Terminal block	440 x 130 x 685 / 48				
	IPS	6000VA/5400W	Tower (Rack option)	Eaton 9PX 6000i HotSwap	9PX6KiBP	2 years	USB/Serial/Slot	3 IEC 10A + 2 IEC 16A + Terminal block	440 x 130 x 685 / 48				
	IPS	8000VA/7200W	Tower (Rack option)	Eaton 9PX 8000i HotSwap	9PX8KiBP	2 years	USB/Serial/Slot	4 IEC 16A + Terminal block	440 x 260 x 700 / 84				
	IPS	11kVA/10kW	Tower (Rack option)	Eaton 9PX 11000i HotSwap	9PX11KiBP	2 years	USB/Serial/Slot	4 IEC 16A + Terminal block	440 x 260 x 700 / 86				
		Eaton 9PX 3:1		IPS	5000VA/4500W	Rack/Tower convertible	Eaton 9PX 5000i RT3U Netpack	9PX5KiRTN	2 years	USB/Serial/Network-MS card	8 IEC 10A + 2 IEC 16A + Terminal block	440 x 130 x 685 / 48	
		IPS	6000VA/5400W	Rack/Tower convertible	Eaton 9PX 6000i RT3U Netpack	9PX6KiRTN	2 years	USB/Serial/Network-MS card	8 IEC 10A + 2 IEC 16A + Terminal block	440 x 130 x 685 / 48			
IPS		8000VA/7200W	Rack/Tower convertible	Eaton 9PX 8000i RT6U HotSwap Netpack	9PX8KiRTNBP	2 years	USB/Serial/Network-MS card	4 IEC 16A + Terminal block	440 x 260 x 700 / 84				
IPS		11kVA/10kW	Rack/Tower convertible	Eaton 9PX 11000i RT6U HotSwap Netpack	9PX11KiRTNBP	2 years	USB/Serial/Network-MS card	4 IEC 16A + Terminal block	440 x 260 x 700 / 86				
		Eaton 93PS		IPS	6000VA/5400W	Tower (Rack option)	Eaton 9PX 6000i 3:1 HotSwap	9PX6KiBP31	2 years	USB/Serial/Slot	4 IEC 16A + Terminal block	440 x 260 x 700 / 88	
		IPS	8000VA/7200W	Tower (Rack option)	Eaton 9PX 8000i 3:1 HotSwap	9PX8KiBP31	2 years	USB/Serial/Slot	4 IEC 16A + Terminal block	440 x 260 x 700 / 88			
		IPS	11kVA/10kW	Tower (Rack option)	Eaton 9PX 11000i 3:1 HotSwap	9PX11KiBP31	2 years	USB/Serial/Slot	4 IEC 16A + Terminal block	440 x 260 x 700 / 88			
		IPS	6000VA/5400W	Rack/Tower convertible	Eaton 9PX 6000i 3:1 HotSwap Netpack	9PX6KiRTNBP31	2 years	USB/Serial/Network-MS card	4 IEC 16A + Terminal block	440 x 260 x 700 / 88			
		IPS	8000VA/7200W	Rack/Tower convertible	Eaton 9PX 8000i RT6U 3:1 HotSwap Netpack	9PX8KiRTNBP31	2 years	USB/Serial/Network-MS card	4 IEC 16A + Terminal block	440 x 260 x 700 / 88			
		IPS	11kVA/10kW	Rack/Tower convertible	Eaton 9PX 11000i RT6U 3:1 HotSwap Netpack	9PX11KiRTNBP31	2 years	USB/Serial/Network-MS card	4 IEC 16A + Terminal block	440 x 260 x 700 / 88			
		Datacentre and Facility UPS											
			Eaton 93PM		IPS	8kVA / 8kW	Tower	93PS-8(20)-15-1x9Ah-6	BA80AA206A01100000	12 months	Serial/Web&SNMP	3ph + N + PE	1300 x 335 x 750 / 171
IPS			10kVA / 10kW	Tower	93PS-10(20)-15-1x9Ah-6	BA01AA206A01100000	12 months	Serial/Web&SNMP	3ph + N + PE	1300 x 335 x 750 / 171			
IPS			15kVA / 15kW	Tower	93PS-15(20)-15-2x9Ah-6	BA51AB206A01100000	12 months	Serial/Web&SNMP	3ph + N + PE	1300 x 335 x 750 / 252			
IPS	20kVA / 20kW		Tower	93PS-20(20)-20-2x9Ah-6	BA02AB206A01000000	12 months	Serial/Web&SNMP	3ph + N + PE	1300 x 335 x 750 / 252				
IPS	30kVA / 30kW		Tower	93PS-30(40)-30-3x9Ah-6	BD03AC206A01100000	12 months	Serial/Web&SNMP	3ph + N + PE	1750 x 480 x 750 / 451				
IPS	40kVA / 40kW		Tower	93PS-40(40)-40-4x9Ah-6	BD04AD206A01000000	12 months	Serial/Web&SNMP	3ph + N + PE	1750 x 480 x 750 / 532				
IPS	30kVA / 30 kW		Tower	93PM-30(50)-IS-BB-6x9Ah-6	AA03A8206A03000000	12 months	Serial/Web&SNMP	3ph + N + PE	1876 x 560 x 914 / 890				
IPS	40kVA / 40 kW		Tower	93PM-40(50)-IS-BB-6x9Ah-6	AA04A8206A03000000	12 months	Serial/Web&SNMP	3ph + N + PE	1876 x 560 x 914 / 890				
IPS	50kVA / 50 kW		Tower	93PM-50(50)-IS-BB-6x9Ah-6	AA05A8206A03000000	12 months	Serial/Web&SNMP	3ph + N + PE	1876 x 560 x 914 / 890				
IPS	60kVA / 54 kW		Tower	93PM-60(60)-IS-BB-6x9Ah-6	AA06A8206A03000000	12 months	Serial/Web&SNMP	3ph + N + PE	1876 x 560 x 914 / 890				
	Eaton Blade UPS		IPS	12000VA/12000W	Rack	Eaton Blade UPS (single unit)	ZC1224401100000	12 months	Serial/Slot	Rack Power Module out	261 (6U) x 442 x 660		
	IPS		12000VA/12000W	Rack	Eaton Blade UPS (parallel unit)	ZC122P060100000	12 months	Serial/Slot	in/out + Rack Power Module	261 (6U) x 442 x 660			

KEY:  Intelligent Power Software  Eaton UPS Companion

* 2 years for batteries

Rack power distribution units (PDU)

Eaton ePDU®

Reliable power distribution to your rack

Managed ePDUs (MA) – maximum functionality for complete control

- Monitoring: individual outlet, branch and ePDU – V, W, A and kWh (Temperature and humidity optional)
- Switching: individual outlet or group, sequencing and cycling
- Control: via Ethernet and advanced LCD screen on the unit

Switched ePDUs (SW) – remote shutdown and restart of equipment

- Monitoring: V, W, A and kWh for total load and branch (Temperature and humidity optional)
- Switching: individual outlets, on, off, cycling and sequencing
- Control: via Ethernet and advanced LCD screen on the unit

Metered Outlet ePDUs (MO) – detailed information for efficient operations

- Monitoring: individual outlet, branch and ePDU – V, W, A and kWh (Temperature and humidity optional)
- Control: via Ethernet and advanced LCD screen on the unit

Metered Input ePDUs (MI) – remote access and monitoring

- Monitoring: branch and ePDU – V, W, A and kWh (Temperature and humidity optional)
- Control: via Ethernet and advanced LCD screen on the unit



IT Racks

Eaton's RE Series IT racks deliver essential protection for critical IT equipment in network closets & small server rooms through to small & medium data center applications. Designed for fast and easy set-up, the RE Series is provided with features IT specialists need in an affordable, ready-to-go enclosure.

Standard racks include;

- Four infinitely adjustable 19" rails with front U markings.
- A range of standard sizes; 27U, 42U and 47U, widths of 600mm and 800mm and a range of depths.
- Locking swing handle on front and rear door
- Locking side panels
- Top panels with configurable infill plates and cable knock outs on 800mm wide models
- 80% free perforation mesh door on active models
- Split rear doors on all 800mm wide active (vented) models
- Grounding kit and levelling feet
- 2 years standard warranty

Eaton Industries Manufacturing GmbH
EMEA Headquarters
Route de la Longeraie 7
1110 Morges
Switzerland
Eaton.eu

© 2017 Eaton
All Rights Reserved
Publication no. TD153016EN,
UPS Quick Guide IEC 2016
February 2017

EATON
Powering Business Worldwide

Software

Intelligent Power Manager/Protector

UPS management software for supervision and system shutdown.

- Easy management of multiple UPSs and ePDUs
- Simple to deploy and learn
- Intuitive web-based interface enables access from anywhere in the network
- Integration with VMware vCenter, XenCenter and Microsoft Hyper-V MSCVMM
- Supports NetApp and EMC storage devices
- Controlled, graceful shutdown of a computer or a server powered by a UPS unit
- Allows work in progress to be saved and data to be preserved



Microsoft Partner Network

UPS companion

- Safe system shutdown
- Energy use and energy cost reporting
- Easy access to UPS status and events
- Configuration of UPS parameters

IPM Infrastructure

Embedded within an Eaton Intelligent Power Controller, the new IPM Infrastructure software provides an easy to use and simple to deploy infrastructure monitoring solution. From the rack view to the data center dashboard the IPM Infrastructure allows IT professionals understand and monitor data center power, environmental and physical capacity metrics, all within the context of their IT infrastructure.



Distributed Services:

Eaton offers a range of warranties and service extensions for plug-and-play and hardwired UPSs in up to 200kVA power range through its extensive IT channel network.

The different options available mean that customers can choose the most beneficial method to safeguard their equipment performance and reliability.

Learn more about Eaton distributed services at www.eaton.eu/upsservices

www.eaton.eu/powerquality

Eaton is a registered trademark of Eaton Corporation.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

