



Maximum weights and floor loading	30-50 kW without internal transformer	30-50 kW with internal transformer	30-50 kW with 2 internal transformers	80-100 kW without internal transformer
Shipping weight	350 kg	590 kg	830 kg	430 kg
Installed weight	290 kg	530 kg	770 kg	370 kg
Floor loading	565 kg/m <sup>2</sup>	1030 kg/m <sup>2</sup>	1500 kg/m <sup>2</sup>	720 kg/m <sup>2</sup>

**METRIC** **EATON CORPORATION**

THIRD ANGLE PROJECTION

DESCRIPTION: D 9PHD UPS 30-100 KW INDUSTRIAL IP23/33 WITH TOP AIR EXHAUST

ORIGINATED: ALAPASSI T. 30 DEC 2015 ECO: NAME: REVISION: 001 SIZE: A2

MODIFIED: SCALE: 3:50

CHECKED: DOCUMENT TYPE: HPO-1042257 STATE: RELEASE SHEET: 1 OF 1

SAFETY: PRO-E DRAWING

APPROVED:

EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY

NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT, INCLUDING THE DRAWING AND INFORMATION CONTAINED THEREON, IS CONFIDENTIAL AND IS THE EXCLUSIVE PROPERTY OF EATON CORPORATION, AND IS MERELY ON LOAN AND SUBJECT TO RECALL BY EATON AT ANY TIME. BY TAKING POSSESSION OF THIS DOCUMENT, THE RECIPIENT ACKNOWLEDGES AND AGREES THAT THIS DOCUMENT CANNOT BE USED IN ANY MANNER ADVERSE TO THE INTERESTS OF EATON AND THAT NO PORTION OF THIS DOCUMENT MAY BE COPIED OR OTHERWISE REPRODUCED WITHOUT THE PRIOR WRITTEN CONSENT OF EATON. IN THE CASE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT.