

Eaton 9PX UPS bundles

Configuration overview

Delivering premium backup power and scalable battery runtimes for servers, voice/data networks and storage systems, the Eaton® 9PX UPS is the ideal solution for both rack and stand-alone installations.



5 and 6 kVA 208V output

Catalog number	Bundle contents	Description	Power rating (VA/watts)	Input plug	Output receptacles	Rack height
9PX5K	9PX5K	5 kVA UPS	5000/4500	Terminal block with L6-30P cord	Hardwired + (2) L6-30R, (2) L6-20R	3U
9PX6K	9PX6K	6 kVA UPS	6000/5400	Terminal block with L6-30P cord	Hardwired + (2) L6-30R, (2) L6-20R	3U
9PX6KG	9PX6KG	6 kVA UPS Global	6000/5400	Hardwired	Hardwired + (2) C19, (8) C13	3U



5 and 6 kVA 120/208V output

Catalog number	Bundle contents	Description	Power rating (VA/watts)	Input plug	Output receptacles	Rack height
9PX5KTF5	9PX5K 9PXTFMR5	5 kVA UPS 5 kVA Transformer	5000/4500	Terminal block with L6-30P cord	Hardwired + (1) L6-30R, (2) L6-20R, (18) 5-20R	6U
9PX6KTF5	9PX6K 9PXTFMR5	6 kVA UPS 5 kVA Transformer	6000/5400	Terminal block with L6-30P cord	Hardwired + (1) L6-30R, (2) L6-20R, (18) 5-20R	6U



5 and 6 kVA 120/208V output with maintenance bypass

Catalog number	Bundle contents	Description	Power rating (VA/watts)	Input plug	Output receptacles	Rack height
9PX5KP1	9PX5K 9PXPPDM1	5 kVA UPS 6 kVA PPDM (plug and play model for rackmount applications)	5000/4500	L6-30P	(1) L14-30R, (1) L6-30R, (6) 5-20R	6U
9PX5KP2	9PX5K 9PXPPDM2	5 kVA UPS 6 kVA PPDM (hardwired model for installations using conduit)	5000/4500	Hardwired	Hardwired	6U
9PX6KP1	9PX6K 9PXPPDM1	6 kVA UPS 6 kVA PPDM (plug and play model for rackmount applications)	6000/5400	L6-30P	(1) L14-30R, (1) L6-30R, (6) 5-20R	6U
9PX6KP2	9PX6K 9PXPPDM2	6 kVA UPS 6 kVA PPDM (hardwired model for installations using conduit)	6000/5400	Hardwired	Hardwired	6U

PPDM—PowerPass distribution module allows a step-down voltage to 120V to accommodate a variety of IT equipment. The PPDM also provides a maintenance bypass, which allows you to service or replace the entire UPS without powering down IT equipment.

Transformer—Provides 120/240V output through receptacles and/or hardwired output.



Visit Eaton.com/9PX to interact with these 9PX models.



Powering Business Worldwide



8 and 11 kVA 208V output

Catalog number	Bundle contents	Description	Power rating (VA/watts)	Input plug	Output receptacles	Rack height
9PX8KHW	9PX8KPM 9PXEBM240RT	8 kVA Power module 11 kVA EBM	8000/7200	Hardwired	Hardwired	6U
9PX11KHW	9PX11KPM 9PXEBM240RT	11 kVA Power module 11 kVA EBM	11000/10000	Hardwired	Hardwired	6U
9PX8K	9PX8KPM 9PXEBM240RT MBP11K208	8 kVA Power module 11 kVA EBM 11 kVA MBP	8000/7200	Hardwired	Hardwired + (3) L6-30R	6U
9PX11K	9PX11KPM 9PXEBM240RT MBP11K208	11 kVA Power module 11 kVA EBM 11 kVA MBP	11000/10000	Hardwired	Hardwired + (3) L6-30R	6U



8 and 11 kVA 120/208V output

Catalog number	Bundle contents	Description	Power rating (VA/watts)	Input plug	Output receptacles	Rack height
9PX8KTF5	9PX8KPM 9PXEBM240RT MBP11K208 9PXTFMR5	8 kVA Power module 11 kVA EBM 11 kVA MBP 5 kVA Transformer	8000/7200	Hardwired	(2) L6-30R, (18) 5-20R	9U
9PX11KTF5	9PX11KPM 9PXEBM240RT MBP11K208 9PXTFMR5	11 kVA Power module 11 kVA EBM 11 kVA MBP 5 kVA Transformer	11000/10000	Hardwired	(2) L6-30R, (18) 5-20R	9U
9PX11KTF11	9PX11KPM 9PXEBM240RT 9PXTFMR11	11 kVA Power module 11 kVA EBM 11 kVA Transformer	11000/10000	Hardwired	Hardwired + (2) L14-30R, (8) 5-20R	9U

Power module—The 8 and 11 kVA 9PX UPSs are composed of one power module (electronics only) and one external battery module (EBM).

MBP—Maintenance bypass switch allows for easy transition between UPS mode and bypass mode in order to perform maintenance. MBP also provides (3) L6-30R output receptacles.



Visit Eaton.com/9PX
to interact with these
9PX models.