



CABLE LENGTH SHOWN NOT TO SCALE




CIRCUIT SCHEMATIC



EBAB03 G3+ BASIC

| | | | |
|---|--|--|-----------------|
| FUNCTIONALITY | INPUT | OUTPUT | ENVIRONMENTAL |
| NONE | 1Ø; 200-240V~; W+N+PE 50/60Hz 10A | (16) IEC 60320 C13 GRIP / P-LOCK | 0 TO 60 °C |
| MECHANICAL | INPUT RATING | OUTPUT RATING | CERTIFICATIONS |
| LENGTH: 704MM WIDTH: 52 MM DEPTH: 53MM ALUMINIUM CHASSIS, BLACK MNT PATTERN SK-23919-Y1 | IEC 60309 C14 10A 230V~ W+N+PE 1.5MM HO5 POWER CORD CABLE LENGTH: 3.0 M | 200-240V~; 50/60Hz 10A PER C13 10A MAX TOTAL | CE, CB |
| CIRCUIT BREAKERS | FILTER AND SPIKE/SURGE | ACCESSORIES | CONFIGURATION |
| NONE | NONE | STANDARD KSP026 - VERT INSTALLATION PACK KA35 | EBA3CP8FABE72AM |



PICTORIAL VIEW
SCALE 0.400

| | | | | |
|---|---|-------------------------------|---|--------------------------------------|
| 02 | CHANGE PACK FROM KSP015 TO KSP025 | 21.05.2019 | AEK | MB |
| 01 | REVISED ACCESSORIES IN SPECIFICATION TABLE. | 12.06.2015 | G.McD. | M.B |
| 00 | INITIAL RELEASE | 12.05.2014 | RA | MB |
| REV. MODIFICATION | | DATE | DESIGNER | VERIF. |
| | | HEINEMANN PRODUCTS | | VUE/VIEW 1ST ANGLE |
| | | CH-1345 LE LIEU SWITZERLAND | | ECHELLE / SCALE 4/10 |
| TOLERANCE GENERALE / GENERAL TOLERANCE | | N/A | N/A | VERIFIE PAR / VERIFIED BY |
| TRAITEMENT / FINISH | | N/A | N/A | N° MAG EBAB03 |
| MATIERE / MATERIAL | | N/A | N/A | DESSINE LE / DRAWN THE 12.05.2014 |
| NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT | | N/A | N/A | PAR / BY RA |
| DESIGNATION | | EPDU BA 0U (C14 10A 1P)16XC13 | | NUMERO DU PLAN PLAN NUMBER |
| COTES A CONTROLER INSPECTION DIMENSIONS | | XX.XX | COTES FONCTIONNELLES FUNCTIONAL DIMENSIONS | # XX.XX |
| Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation. This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization. | | | | |