



CABLE LENGTH SHOWN NOT TO SCALE



| EILB13 | | G3+ INLINE METERED | |
|--|---|---|-----------------|
| FUNCTIONALITY | INPUT | OUTPUT | ENVIRONMENTAL |
| CURRENT POWER AND ENERGY METERING | IEC 60309-2 16A 230V~ W+N+PE (M) 1.5MM HO5 POWER CORD CABLE LENGTH: 3.0 M | IEC 60309-2 16A 230V~ W+N+PE (F) 1.5MM HO5 POWER CORD CABLE LENGTH: 3.0 M | 0 TO 60° C |
| MECHANICAL | INPUT RATING | OUTPUT RATING | CERTIFICATIONS |
| LENGTH: 443 MM WIDTH: 52 MM DEPTH: 53MM ALUMINIUM CHASSIS, BLACK MNT PATTERN SK-23919-Y1 | 1Ø; 200-240V~;W+N+PE 50/60HZ 16A | 1Ø; 200-240V~;W+N+PE 50/60HZ 16A | CE, CB |
| CIRCUIT BREAKERS | FILTER AND SPIKE/SURGE | ACCESSORIES | CONFIGURATION |
| NONE | NONE | STANDARD KSP016 - EMEA HOR INSTALL NETWORK PACK OPTIONAL EMPDT1H1C2 - ENVIRONMENTAL PROBE | EIL3CEHFAAA71AM |



PICTORIAL VIEW
SCALE 0.200

| | | | | |
|---|---|--|----------|------------------------------|
| 03 | VIEW WITH NEW BRACKET | 26.07.2017 | VV | MB |
| 02 | REVISED DIMENSIONS FOR MOUNTING BRACKETS. | 09.06.2015 | G.McD. | M.B. |
| 01 | REVISED TO FIX GRAPHICS. | 21.05.2014 | G.McD. | M.B. |
| 00 | INITIAL RELEASE. | 06.03.2014 | | M.B. |
| REV. | MODIFICATION | DATE | DESIGNER | VERIF. |
| | | HEINEMANN PRODUCTS | | VUE/VIEW |
| | | CH-1345 LE LIEU SWITZERLAND | | EUROPE |
| TRAITEMENT / FINISH NA | | ECHELLE / SCALE 4/10 | | N° MAG EILB13 |
| MATIERE / MATERIAL NA | | DESSINE LE / DRAWED THE 06.03.2014 | | PAR / BY |
| TOLERANCE GENERALE / GENERAL TOLERANCE | | VERIFIE PAR / VERIFIED BY | | M.B. |
| NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT X | | DIMENSIONS AND TOLERANCES IN MILLIMETERS | | |
| DESIGNATION EPDU IL 0U (309 16A 1P)1X309 | | SK-30919-Y1 | | 03 |
| COTES A CONTROLER / INSPECTION DIMENSIONS XX.XX | | COTES FONCTIONNELLES / FUNCTIONAL DIMENSIONS # XX.XX | | NUMERO DU PLAN / PLAN NUMBER |
| <small>Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation. This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.</small> | | | | |