



PICTORIAL VIEW
SCALE 0.200

EILB15		G3+ INLINE METERED	
FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT POWER AND ENERGY METERING	IEC 60309-2 32A 400V~ WYE, 3W+N+PE (M) 4.0MM HO7 POWER CORD CABLE LENGTH: 3.0M	IEC 60309-2 32A 400V~ WYE, 3W+N+PE (F) 4.0MM HO7 POWER CORD CABLE LENGTH: 3.0M	0 TO 60° C
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
LENGTH: 443MM WIDTH: 52 MM DEPTH: 53MM ALUMINIUM CHASSIS, BLACK MNT PATTERN SK-23919-Y1	3Ø;346-415V~ WYE, 3W+N+PE 50/60HZ 32A	3Ø;346-415V~ WYE, 3W+N+PE 50/60HZ 32A	CE, CB
CIRCUIT BREAKERS	FILTER AND SPIKE/SURGE	ACCESSORIES	CONFIGURATION
NONE	NONE	STANDARD KSP016 - EMEA HOR INSTALL AND NETWORK PACK OPTIONAL EMPDT1H1C2 - ENVIRONMENTAL PROBE	EIL3DHJFAAA71AM

03	VIEW WITH NEW BRACKET	26.07.2017	VV	MB
02	REVISED DIMENSIONS FORMOUNTING BRACKETS.	09.06.2015	G.McD.	M.B.
01	REVISED TO FIX GRAPHICS.	21.05.2014	G.McD.	M.B.
REV	MODIFICATION	DATE	DESIGNER	VERIF
		HEINEMANN PRODUCTS		VUE/VIEW EUROPE: 4/10
		CH-1345 LE LIEU SWITZERLAND		N° MAG: EILB15
TOLERANCE GENERALE / GENERAL TOLERANCE		VERIFIE PAR / VERIFIED BY		M.B.
TRAITEMENT / FINISH: NA		DESSINE LE / DRAWN THE: 06.03.2014		
MATIERE / MATERIAL: NA		PAR / BY		
NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT: X			DIMENSIONS AND TOLERANCES IN MILLIMETERS	
DESIGNATION: EPDU IL 0U (309 32A 3P)1X309		SK-31119-Y1		03
COTES A CONTROLER / INSPECTION DIMENSIONS: XX.XX		COTES FONCTIONNELLES / FUNCTIONAL DIMENSIONS: # XX.XX		NUMERO DU PLAN / PLAN NUMBER
Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation. This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.				