

EMAB12


General

Style Number	EMAB12
Part Number	EMAB12
Availability	Usually in stock
U Height	42 [Minimum U rack]
MIB	available for download



Physical

Dimensions (H x W x D, mm)	52x65x1829
Mounting Style	Button mounting on rear and sides, variable mounting bracket included
Form factor	0U

Input

Max kW	22
Plug	(1) IEC 60309 32A 3P 
Cable Length (m)	3
Voltage	400V
Current	32A 3P
Phase	Three-phase
Frequency	50Hz

Output

Grip cable retention	Yes
Outlets	(12) IEC-320-C13 (12) IEC-320-C19  
Circuit Breakers	6 single pole
Outlet Control	Yes

Protection & Filtering

Spike/Surge Suppression	None
EMI/RFI Filter	None

Control & Interface

Daisy Chain	8 ePDUs
Operating Temperature	60 Degrees C
Hot Swap Network and Control	Yes
Communication and Protocols	HTTP, HTTPS, SSL, Telnet, FTP, SNMP, SMTP, DNS, DHCP, LDAP, RADIUS
Optional Temperature and Humidity probe	EMP001
Environmental Interface	Yes
Serial Interface	Yes
Ethernet Interface	Yes
Voltage Monitoring	Yes

Metering and Switching

Metering	Outlet and Equipment Monitoring across A and B feed
Metering Characteristics	V, W, A and kWhr, Active power, Apparent Power, Peak Power
Metering Accuracy	IEC Class 1 Billing grade Accuracy
Level 3 PUE measurements	Yes
Circuit breaker status monitoring	Yes
Switching	Outlet and Equipment Switching across A and B feed

Environmental & Approval Standards

Approvals	CB, CE, EN 60950-1:2006/A11:2009/A1:2010/A12:2011 Safety - Part 1: General Requirements, IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1 EN 55022:2010 Radio Disturbance characteristics - Limits and methods of measurement. EN 55024:2010 Immunity characteristics - Limits and methods of measurement.
Electromagnetic compatibility	EN 61000-6-2:2005 Part 6-2: Generic standards - Immunity for industrial environments EN 61000-6-4:2007+A1:2011 Part 6-4: Generic standards - Emission standard for industrial environments
Environmental	RoHS Directive – 2011/65/EU, EN 50581 : 2012, REACH Regulation (CE No. 1907/2006), WEEE directive 2012/19/EU, PEP ecopassport (Basic ePDUs) Packaging: 100% recycled, 100% recyclable: no plastic, no metal, no foam.
Manufacturing Plant	ISO 9001:2008 / ISO 14001:2004

Warranty

Standard warranty

2 years

[Privacy Policy](#)
[Terms & Conditions](#)
[Copyright](#)

© 2019 Eaton
All Rights Reserved