



CABLE LENGTH SHOWN NOT TO SCALE



EILB24 G3 INLINE METERED, DUAL SOURCE

FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT POWER AND ENERGY METERING FOR TWO ELECTRICAL SOURCES	2 SOURCES. EACH: IEC 60309-2 16A 230V~ W+N+PE (M) 1.5MM HO5 POWER CORD CABLE LENGTH: 3.0 M	2 SOURCES. EACH: IEC 60309-2 16A 230V~ W+N+PE (F) 1.5MM HO5 POWER CORD CABLE LENGTH: 3.0 M	0 TO 60° C
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
LENGTH: 443 MM WIDTH: 52 MM DEPTH: 65MM ALUMINIUM CHASSIS, BLACK MNT PATTERN SK-23919-Y1	2 SOURCES. EACH: 1Ø; 200-240V~;W+N+PE 50/60HZ 16A	2 SOURCES. EACH: 1Ø; 200-240V~;W+N+PE 50/60HZ 16A	CE, CB
CIRCUIT BREAKERS	FILTER AND SPIKE/SURGE	ACCESSORIES	CONFIGURATION
NONE	NONE	STANDARD KSP016 - EMEA HOR INSTALL NETWORK PACK OPTIONAL EMP001 - ENVIRONMENTAL PROBE	EIL3YEHFAAA81AM



PICTORIAL VIEW
SCALE 0.200

REV. MODIFICATION		DATE	DESIGNER	VERIF.
HEINEMANN PRODUCTS		EUROPE	4/10	EILB24
CH-1345 LE LIEU SWITZERLAND		DESIGNED BY / DRAWN THE	23.03.2015	
		PAR / BY	G.McD.	
TOLERANCE GENERALE / GENERAL TOLERANCE		VERIFIE PAR / VERIFIED BY		
TRAITEMENT / FINISH		NA		
MATIERE / MATERIAL		NA		
NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT		X	DIMENSIONS AND TOLERANCES IN MILLIMETERS	
DESIGNATION		EPDU IL 0U (309 16A 1P)2X309	SK-73419-Y1	00
COTES A CONTROLER INSPECTION DIMENSIONS	XX.XX	COTES FONCTIONNELLES FUNCTIONAL DIMENSIONS	# XX.XX	NUMERO DU PLAN PLAN NUMBER
Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation. This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.				