


EVMAGU23X-3 G3 UPDU MANAGED

FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT, POWER, AND ENERGY METERING FOR INPUT, BRANCH AND OUTLET; OUTLET SWITCHING	EATON/SOURIAU UTG SERIES 8-PIN CONNECTOR CORDSETS NOT INCLUDED, MUST BE ORDERED SEPARATELY	(24) IEC 60320 C13 (18) EATON C39 - COMBO C13/C19	0° TO 60° C 32° TO 140° F
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
72.01" (1829mm) LENGTH 2.05" (52mm) WIDTH 2.56" (65mm) DEPTH ALUMINUM CHASSIS, BLACK	1P: 100-240V~, 16-63A, or 3P DELTA: 100-240V~, 16-55A, or 3P WYE: 100-240 / 173-415V~, 16-32A 50/60Hz; USE WITH EZ1 SERIES CORDSET (CBL3XX-XX)	100-240V~; 10A PER C13, 16A PER C39 16A MAX PER SECTION NOT TO EXCEED INPUT CORDSET RATING	cTUVus CE, UKCA, RCM
CIRCUIT BREAKERS	COMMUNICATION	ACCESSORIES	REGULATORY MODEL
(6) 20A 2-POLE LISTED	G3 eNMC WITH 10/100 ETHERNET, LCD, SERIAL, USB, 1 + 3 DAISY-CHAIN	INCLUDED SPK045 - INSTALLATION OPTIONAL SPK013 - COMM CABLES OPTIONAL EMPDT1H1C2 - ENVIRONMENTAL PROBE	EMAF-ZBAK-G28K



METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER):	REVISION:	EATON
		9001-22344_EVMAGU23X-3	01	
DESCRIPTION: PDU G3 0U UNV23KW 24xC13, 18xC39		SIZE: D		
ORIGINATED BY: R. SIEGFRIED	11 OCT 2022	SEE NOTES FOR TOLERANCES. DIM ARE IN MM (INCHES) AFTER PLATING	STATE: PRELIMINARY	SCALE: 0.400
MODIFIED BY: R. SIEGFRIED	11 OCT 2022	INTERPRET DIM AND TOL PER ASME Y14.5-2018	ECO:XXXX	SHEET: 1 OF 1