



SCALE 0.333



SCALE 0.333



LINE CORD LENGTH OPTIONAL
6, 10, 15 & 20 FT LENGTHS AVAILABLE

**RPM-3U WITH IEC 309 60A LINE CORD
(OPTIONAL CABLE TRAY AND MOUNTING BRACKETS NOT SHOWN)**

METRIC		THIRD ANGLE PROJECTION	POWERWARE	SIZE: D
DESCRIPTION: ASSY DWG, R2P2				
MODIFIED BY: M. CARNES	DATE: 28-MAY-2007	UNLESS OTHERWISE SPECIFIED TOLERANCES ON DIMENSIONS ARE: ANGLES: ±1/2° DECIMALS: 0.X: ±0.25 X (FOR 1 < X ≤ 3): ±1 HOLES: Ø&0.13 0.XX: ±0.25 X (FOR X > 3): ±2.5 DIMENSIONS ARE IN MILLIMETERS (INCHES) AND AFTER PLATING		SCALE: 1:1000 DO NOT SCALE DRAWING OR CHANGE MANUALLY
ECO: 000XXXX	STATE: Preliminary	PRO-ENGINEER GENERATED		PART NAME: MARKETING.DWG
		REVISION: 2	SHEET: 2 of 8	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF POWERWARE CORP. AND SHALL NOT BE REPRODUCED OR COPIED OR USED AS THE BASIS FOR MANUFACTURE OR SALE OF APPARATUS WITHOUT PERMISSION				