






P O N M L K J I H G F E D C B A



EVMAFC20A	G4 Rack PDU MANAGED		
FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT, POWER, AND ENERGY METERING FOR INPUT, BRANCH AND OUTLET; OUTLET SWITCHING	IEC 60309 C20 16A 100/240V 1.5MM ² HO5 POWERCORD CABLE LENGTH: 3.0 M	(12) IEC 60320 C13 HIGH RETENTION / P-LOCK (12) EATON C39 - COMBO C13/C19 HIGH RETENTION / P-LOCK (C19 ONLY)	0° TO 60° C 32° TO 140° F
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
1000mm (39.37") LENGTH 52mm (2.05") WIDTH 53mm (2.09") DEPTH ALUMINUM CHASSIS, BLACK	100-240V~ W+N+PE OR 2W+PE 16A 50/60HZ	100-240V~ 10A PER C13;16A PER C39 16A MAX PER SECTION 16A MAX TOTAL	cTUVus,CE, UKCA, RCM
CIRCUIT BREAKERS	COMMUNICATION	ACCESSORIES	REGULATORY MODEL
NONE	G4 NMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY	SPARE PART ACCESSORY KIT SPK050 OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2 SPARE PART G4 NMC SPK055	EMAF-JXFA-A31K

03 GLOBAL UPDATE		26.10.2023	RP	YS
00 FIRST RELEASE		10.08.2023	RP	YS
REV. MODIFICATION	DATE	DESSINER	VERIF.	
EATON		HEINEMANN PRODUCTS	ECHELLE / SCALE	N° MAG
CH-1345 LE LIEU SWITZERLAND		1/2	9001-22334	
TRAITEMENT / FINISH NA		DESSINE LE / DRAWN THE	10.08.2023	
MATIERE / MATERIAL NA		PAR / BY	RP	
TOLERANCE GENERALE / GENERAL TOLERANCE ± 0.3 ± 0'20"		VERIFIE PAR / VERIFIED BY	YS	
NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT X		DIMENSIONS AND TOLERANCES IN MILLIMETERS		
DESIGNATION	PDU G4 MA 0U C20Plug 12xC13,12xC39	9001-22334_EVMAFC20A	03	
COTES A CONTROLER / INSPECTION DIMENSIONS	XX.X	COTES FONCTIONNELLES / FUNCTIONAL DIMENSIONS	XX.X	NUMERO DU PLAN / PLAN NUMBER
Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation.		This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.		

P O N M L K J I H G F E D C B A