



<b>EVSWF316A</b>	<b>G4 Rack PDU SWITCHED</b>		
<b>FUNCTIONALITY</b>	<b>INPUT</b>	<b>OUTPUT</b>	<b>ENVIRONMENTAL</b>
CURRENT POWER AND ENERGY METERING FOR INPUT AND BRANCH; INDIVIDUAL OUTLET CONTROL	IEC 60309-2 16A 230/400V 2.5MM <sup>2</sup> x 5C POWERCORD (LSZH) CABLE LENGTH: 3.0 M	(12) IEC 60320 C13 HIGH RETENTION / P-LOCK (12) EATON C39 - COMBO C13/C19 HIGH RETENTION / P-LOCK (C19 ONLY) ALTERNATING PHASES	0° TO 60° C 32° TO 140° F
<b>MECHANICAL</b>	<b>INPUT RATING</b>	<b>OUTPUT RATING</b>	<b>CERTIFICATIONS</b>
1000mm (39.37") LENGTH 52mm (2.05") WIDTH 53mm (2.09") DEPTH ALUMINUM CHASSIS, BLACK	200-240 / 346-415V~ WYE, 3W+N+PE 16A 50/60Hz	200-240V~ 10A PER C13, 16A PER C39 16A MAX PER SECTION NOT TO EXCEED INPUT RATING	CE, UKCA, RCM, Cmim, Ukr, EAC
<b>CIRCUIT BREAKERS</b>	<b>COMMUNICATION</b>	<b>ACCESSORIES</b>	<b>REGULATORY MODEL</b>
NONE	G4 NMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY UL 2900-1 and IEC 62443-4-2	SPARE PART ACCESSORY KIT SPK050 OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2 SPARE PART G4 NMC SPK055	ESWF-DAFA-A31K

HEINEMANN PRODUCTS		EATON	
CH-1345 LE LIEU SWITZERLAND		9001-22360	
DESIGNATION: PDU G4 SW 0U 309 16A 3P 12xC13,12xC39		9001-22360_EVSWF316A 01	
DATE: 06.10.2023		DATE: 06.10.2023	
PAR / BY: RP		VERIFIE PAR / VERIFIED BY: YS	
ECHELLE / SCALE: 1/2		N° MAG: 9001-22360	
TRAITEMENT / FINISH: NA		DIMENSIONS AND TOLERANCES IN MILLIMETERS	
MATERIE / MATERIAL: NA		X	
COTES A CONTROLER / INSPECTION DIMENSIONS: XX.X		COTES FONCTIONNELLES / FUNCTIONAL DIMENSIONS: XX.X	
Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation.		This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.	