



<b>EVMAF332C</b>	<b>G4 Rack PDU MANAGED</b>		
<b>FUNCTIONALITY</b>	<b>INPUT</b>	<b>OUTPUT</b>	<b>ENVIRONMENTAL</b>
CURRENT, POWER, AND ENERGY METERING FOR INPUT, BRANCH AND OUTLET; OUTLET SWITCHING	IEC 60309-2 32A 230/400V 6MM <sup>2</sup> x 5C POWERCORD (LSZH) CABLE LENGTH: 3.0M	(24) IEC 60320 C13 HIGH RETENTION / P-LOCK (24) EATON C39 - COMBO C13/C19 HIGH RETENTION / P-LOCK (C19 ONLY) ALTERNATING PHASES	OPERATING TEMPERATURE 0° TO 60° C 32° TO 140° F
<b>MECHANICAL</b>	<b>INPUT RATING</b>	<b>OUTPUT RATING</b>	<b>CERTIFICATIONS</b>
1900mm (74.8") LENGTH 52mm (2.05") WIDTH 53mm (2.09") DEPTH ALUMINUM CHASSIS, BLACK	200-240 / 346-415V~ WYE, 3W+N+PE 32A 50/60HZ	200-240V~ 10A PER C13; 16A PER C39 16A MAX PER SECTION NOT TO EXCEED INPUT RATING	CE, UKCA, RCM, Cmm, Ukr, EAC
<b>CIRCUIT BREAKERS</b>	<b>COMMUNICATION</b>	<b>ACCESSORIES</b>	<b>REGULATORY MODEL</b>
(6) 16A 1-POLE	G4 NMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY UL 2900-1 and IEC 62443-4-2	SPARE PART ACCESSORY KIT SPK050 OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2 SPARE PART G4 NMC SPK055	EMAF-DHFB-G49K

01	GLOBAL UPDATE	27.10.2023	RP	YS
00	FIRST RELEASE	10.08.2023	RP	YS
REV	MODIFICATION	DATE	DESIGNER	VERIF
		<b>HEINEMANN PRODUCTS</b> CH-1345 LE LIEU SWITZERLAND		ECHELLE / SCALE 0.4 N° MAG 9001-22373
TRAITEMENT / FINISH NA		DESSINE LE / DRAWN THE 10.08.2023		PAR / BY RP
MATIERE / MATERIAL NA		VERIFIE PAR / VERIFIED BY YS		NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT X
DIMENSIONS AND TOLERANCES IN MILLIMETERS		DESIGNATION PDU G4 MA 0U 309 32A 3P 24xC13,24xC39		
COTES A CONTROLER INSPECTION DIMENSIONS XX.X		COTES FONCTIONNELLES FUNCTIONAL DIMENSIONS XX.X		NUMERO DU PLAN PLAN NUMBER 9001-22373_EVMAF332C
1		00		

Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation.  
This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.