




REV	ECO No.	REVISION	DR	CK	AP	DATE
01	174149	ENGINEERING RELEASE	J.O.			02 JULY 20
02	188584	REVISED REVISION	R.S.			02 JULY 20



PC3554R REMOTE EPO

FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
POWER CONTROLLER WITH STANDARD REMOTE	NEMA L21-30 PLUG 15FT 10AWG / 5C POWERCORD	(6) NEMA 5-20, SWITCHED (2) NEMA 5-20, UNSWITCHED (3) NEMA L21-30, SWITCHED	32° TO 113° F 0° TO 45° C
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
19.00" (482.7mm) WIDTH 3.44" (87.4mm) HEIGHT 14.50 (368.3mm) DEPTH BLACK CHASSIS	120/208V ~ 3P + N + PE 24A 50/60HZ	J5-J6, J8-J9, J11-J12, J13-J14: 120V ~; 16A J4, J7, J10: 120/208V ~ 24A 24A MAX PER SECTION 24A PER PHASE	
CIRCUIT BREAKERS	FILTER AND SPIKE/SURGE	INDICATOR LIGHTS: SEVEN GREEN	ACCESSORIES INCLUDED
MAIN (1) 30A 3-POLE LISTED BRANCH (4) 20A 1-POLE LISTED	EMI/RFI FILTER COMMON AND DIFFERENTIAL MODE SPIKE/SURGE PROTECTION	THREE FOR MAIN POWER PHASES; ONE GREEN, FOR EACH BRANCH BREAKER	SUB-HRDWARE-001 - PANEL MOUNT KIT SCREWS SUB-HRDWARE-007 - 2-PT CONNECTORS SPK030 - PANEL MOUNT KIT CAGE NUTS REMTE02 - REMOTE CONNECTOR KIT (4)



STANDARD REMOTE: REMOTE AND LOCAL START.
SELECTABLE MTD ON/OFF

METRIC		THIRD ANGLE PROJECTION		EATON CORPORATION, ELECTRICAL		EATON		SIZE D
SPECIFICATION DRAWING PC3554R								
MODIFIED BY: J. OSBORNE	DATE: 26 SEPT 19	UNLESS OTHERWISE SPECIFIED TOLERANCES ON DIMENSIONS ARE: ANGLES: ±1/2° DECIMALS: 0.X: ±0.25 X (FOR X < 3): ±1			SCALE: 0.500 DO NOT SCALE			
ECO: 174149	STATE: RELEASE	HOLES: Ø<0.3 Ø<X: ±0.25 X (FOR X > 3): ±2.5 DIMENSIONS ARE IN MILLIMETERS (INCHES) AND AFTER PLATING			DRAWING OR CHANGE MANUALLY			
PRO-ENGINEER GENERATED			PART NAME: PC3554R		REVISION: 02		SHEET: 1 of 1	
<small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION THIS DOCUMENT, INCLUDING THE DRAWING AND INFORMATION CONTAINED THEREON, IS CONFIDENTIAL AND IS THE EXCLUSIVE PROPERTY OF EATON CORPORATION AND IS HEREBY ON LOAN AND SUBJECT TO RECALL BY EATON AT ANY TIME. BY TAKING POSSESSION OF THIS DOCUMENT, THE RECIPIENT ACKNOWLEDGES AND AGREES THAT THIS DOCUMENT CANNOT BE USED IN ANY MANNER ADVERSE TO THE INTERESTS OF EATON, AND THAT NO PORTION OF THIS DOCUMENT MAY BE COPIED OR OTHERWISE REPRODUCED WITHOUT THE PRIOR WRITTEN CONSENT OF EATON. IN THE CASE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2008 Eaton Corporation - All Rights Reserved.</small>								