




LTR	ECO No.	REVISION	DR	CK	AP	AP	DATE
A		RELEASED	J.O.				15 NOV 99
B	8011	UPDATE CHASSIS & TEXT	LS	J.O.			21 OCT 04
C	8309	UPDATE TO RoHS PRODUCT	LS	DK			08 MAY 05
D	8696	UPDATE LOGO & TEXT	J.O.				12 MAY 09
E	12931	UPDATED TITLE BLOCK	GS				23 JUL 10
001	029146	EPO SWITCH UPDATE	KG				31 JAN 12
002	064381	ADD ROHS NOTES	HN				24 APR 14



**NOTES**

1. RACK MOUNTED STEEL CHASSIS, BLACK MEDIUM TEXTURE  
19.00" WIDE FLUSH MOUNTING  
1.72" HIGH  
1.84" DEEP
2. SILK SCREENING:  
TEXT IS WHITE  
YELLOW BACKGROUND AROUND EPO BUTTON
3. EMERGENCY OFF SWITCH: RED MUSHROOM PUSHBUTTON SWITCH.  
PUSH TO ACTIVATE EMERGENCY POWER OFF &  
TURN KNOB CLOCKWISE TO RESET EPO
4. SELECTOR SWITCH: 1 SWITCH, 3-POSITION  
"OFF" TURNS UNIT OFF AND HOLDS OFF  
"ON" TURNS UNIT ON  
"START" IS MOMENTARY AND STARTS UNIT
5. REMOTE CABLE: 22/3 CABLE, 15 FEET LONG WITH 3 PIN CONNECTOR.
6. RoHS COMPLIANT PRODUCT PER DIRECTIVE 2011/65/EU WITH APPLICABLE EXEMPTIONS.
7. ALL MATERIALS AND SUB-MATERIALS COMPLY WITH EATON SPECIFICATION 164080496. DOCUMENTATION CERTIFYING COMPLIANCE TO EATON SPECIFICATION 164080496 IS AVAILABLE UPON REQUEST.



NYCOMED OR SALES APPROVAL \_\_\_\_\_ DATE \_\_\_\_\_

THE INFORMATION AND DESIGN DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF EATON CORPORATION. EATON CORPORATION RESERVES ALL PATENT, PROPRIETARY, DESIGN, MANUFACTURING, REPRODUCTION, USE AND SALE RIGHTS THERETO, AND TO ANY ARTICLE DISCLOSED THEREIN, EXCEPT TO THE EXTENT RIGHTS ARE EXPRESSLY GRANTED TO OTHERS. THE FOREGOING DOES NOT APPLY TO VENDOR PROPRIETARY PARTS. COPYRIGHT 2009 EATON CORP

		9650 Jeronimo Road, Irvine, California 92618 Phone (949) 452-8500 www.epdu.com	
DIMENSIONS IN INCHES TOLERANCES: DECIMALS ANGLES .XX ±0.5° .020 .XXX UNLESS OTHERWISE SPECIFIED .010		TITLE ENGINEERING DRAWING RCP100-BLK-LT ASSY 2604	
DRAWN BY: J OSBORNE DWG FILENAME: RCP_100_BLK_LT_2604_ME.DWG		SCALE: 1:1 SIZE: D SHEET: 1 OF 1 DWG NO.: RCP_100_BLK_LT_2604_ME REV: 002	