




LTR	ECO No.	REVISION	DR	CK	AP	AP	DATE
A		ENGINEERING RELEASE	MDV				07/01/02
B	8018	UPDATE CHASSIS & TEXT	LS		J.O.		27 OCT 04
C	8398	ADD RoHS NOTE	J.O.				08 NOV 06
D	12932	UPDATED EATON LOGO	GS				26 JUL 10
002	064441	ADD ROHS NOTES	HN				25 APR 14



**NOTES**

- RACK MOUNTED STEEL CHASSIS BLACK FED STD 595-27038 MEDIUM TEXTURE  
19.00" WIDE STANDARD RACK MOUNT  
3.44" HIGH  
2.06" DEEP
- INPUT: 120 VAC 12A SINGLE PHASE 50/60 HZ  
POWER CABLE: 6 FOOT 14/3 SJT CABLE WITH NEMA 5-15 PLUG
- OUTPUT: 120 VAC 12A AT ONE NEMA 5-15 RECEPTACLE
- SELECTOR SWITCH: 3-POSITION:  
"OFF" TURNS UNIT OFF AND HOLDS OFF  
"ON" TURNS UNIT ON  
"START" IS MOMENTARY AND STARTS UNIT
- REMOTE CABLE: 15FT 22/3 CABLE WITH 3 PIN CONNECTOR.
- OPERATION: CONNECT TO REMOTE PORT OF POWER CONTROLLER WITH LATCHING REMOTE:



- RoHS COMPLIANT PRODUCT PER DIRECTIVE 2011/65/EU WITH APPLICABLE EXEMPTIONS.
- ALL MATERIALS AND SUB-MATERIALS COMPLY WITH EATON SPECIFICATION 164080496. DOCUMENTATION CERTIFYING COMPLIANCE TO EATON SPECIFICATION 164080496 IS AVAILABLE UPON REQUEST.

SALES APPROVAL \_\_\_\_\_ DATE \_\_\_\_\_

<p>THE INFORMATION AND DESIGN DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF EATON CORPORATION. EATON CORPORATION RESERVES ALL PATENT, PROPRIETARY, DESIGN, MANUFACTURING, REPRODUCTION, USE AND SALE RIGHTS THERETO, AND TO ANY ARTICLE DISCLOSED THEREIN, EXCEPT TO THE EXTENT RIGHTS ARE EXPRESSLY GRANTED TO OTHERS. THE FOREGOING DOES NOT APPLY TO VENDOR PROPRIETARY PARTS. COPYRIGHT 2009 EATON CORP</p>		<p><b>EATON</b> 9650 Jeronimo Road, Irvine, California 92618 Phone (949) 452-8500 www.epdu.com</p>	<p>TITLE ENGINEERING DRAWING RCP 200-BLK-LT ASSY 2823</p>
<p>DIMENSIONS IN INCHES TOLERANCES: DECIMALS ANGLES ±.000 ± 0.5° UNLESS OTHERWISE SPECIFIED CAGE CODE 51795</p>	<p>DRAWN BY: MDV SCALE: 1:1 SIZE: D SHEET: 1 OF 1</p>	<p>DWG FILENAME: RCP_200_BLK_LT_2823_ME DWG NO.: RCP_200_BLK_LT_2823_ME</p>	<p>REV: 002</p>