

GENERAL SPECIFIED


CABINET CHARACTERISTIC:
ENCLOSURE : NEMA 1
LOCATION : INDOOR


MECHANICAL:
MOUNTING: FREESTANDING/FLOORSTAND
MATERIAL: STEEL

WEIGHT : 375 LBS. APPROX.

ELECTRICAL:
OUTOUT PB #1: 42 POLE, BOLT ON CIRCUIT BREAKER (60 A MAX)

ENVIROMENTAL:
OPERATING AMBIENT TEMPERATURE 0°C TO 40°C (32° F TO 104°F)
RELATIVE HUMIDITY: 0% TO 95 % NON-CONDENSING
ALTITUDE: 10,000 FT MAX

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [] IN MILLIMETER ANGULAR: ±0.5° BEND ±1° TWO PLACE DECIMAL ±0.02 THREE PLACE DECIMAL ±0.005		THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF SMITHS POWER	
 THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING	
APPROVALS		DATE	
DRAWN			
CHECKED			
ENG. APPR.			

		
TITLE: (1) 225A NF PANELBOARD (1) CTS MONITOR		
SIZE B	DWG. NO. MCRPP56805	REV A
PART NO.		SHEET 1 OF 1