



**GENERAL SPECIFIED**

**CABINET CHARACTERISTIC:**  
 ENCLOSURE : NEMA 1  
 LOCATION : INDOOR  
 MOUNTING: WALL OR FLOOR MOUNT  
 MATERIAL: STEEL  
 FINISH: EXTERIOR PANELS: POWDER COAT  
 WEIGHT : 175 LBS. APPROX.

**ELECTRICAL:**  
 INPUT : 208 VAC 3PH-4W W/GND @ 60 HZ  
 OUTPUT : 225A- 42 POLE, BOLT ON CIRCUIT BREAKER (60 A MAX)  
 ALL CUSTOMER SUPPLIED CABLE CONNECTION BASE ON 75 °C COPPER WIRE.  
 CONSULT NEC & LOCAL REGULATIONS.

UNLESS OTHERWISE SPECIFIED:  
 DIMENSIONS ARE IN INCHES  
 [ ] IN MILLIMETER  
 ANGULAR: ±0.5° BEND ±1°  
 TWO PLACE DECIMAL ±0.02  
 THREE PLACE DECIMAL ±0.005

THIS DRAWING CONTAINS  
 CONFIDENTIAL & PROPRIETARY  
 INFORMATION AND SHALL NOT  
 BE DISCLOSED OR COPIED  
 WITHOUT THE EXPRESSED,  
 WRITTEN PERMISSION OF  
 SMITHS POWER



THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING	
APPROVALS		DATE	
DRAWN	LJN	3/21/16	
CHECKED			
ENG. APPR.			

TITLE:		
MCRPP MODEL-B (2) 225A-42P SQD-NQ BCMS_WITH MONITOR		
SIZE	DWG. NO.	REV
<b>B</b>	<b>12217026</b>	<b>A</b>
PART NO.		SHEET 1 OF 1