


8 7 6 5 4 3 2 1



MLO INPUT

X2 400A MAIN

MAIN CTS OPTIONAL

INPUT GRD BUS


84.00

X2 SQD NQ 42 P PANELBOARD

BRANCH CTS MONITOR OPTIONAL

OUTPUT GRD BUS

OUTPUT NEUTRAL BUS



x4 Ø.44 MOUNTING HOLES

10.00

22.00


X60 1/2" KNOCK OUT

X 26 DBL 1/2" & 3/4" KNOCK OUT

EXCHANGE ABLE KNOCK OUT PLATE

7" MONITOR DISPLAY OPTIONAL

VIEWABLE DOORS



GENERAL SPECIFIED

ENCLOSURE TYPE : NEMA 1, LOCATION : INDOOR  
 MOUNTING: WALL OR FLOOR  
 MATERIAL: STEEL  
 FINISH: POWDER COAT  
 WEIGHT : 375 LBS. APPROX.  
 ELECTRICAL:  
 INPUT : (2) 208 VAC 3PH-4W W/GND AND NEUTRAL @ 60 HZ, 400A, MAIN LUG ONLY  
 OUTPUT: (2) PANEL BOARD 42 POLE SQD NQ, BOLT ON CIRCUIT BREAKER

THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION, INC.



APPROVALS		DATE
DRAWN	WHS	1/21/16
DESIGNED		
CHECKED	LJN	1/21/16
ENG. APPR.		
MFG. APPR.		

THIRD ANGLE PROJECTION			TITLE: OUTLINE MCRPP		
			(2) 400A 42P SQD NQ WITH MAIN		
SIZE	DWG. NO.	REV			
B	MCP21206	A			
SCALE: NTS		SHEET 1 OF 1			

A

8 7 6 5 4 3 2 1