



REVISIONS				
REV.	ECN #	DESCRIPTION	DATE	APPROVED
X0		SUBMITTAL RELEASE	10/16/19	AD




TOP VIEW



**FRONT VIEW
NO DOORS**


3 FUSE PANEL
BEHIND DOOR



FRONT VIEW


- 3 L-FRAME CB
6X400A OUTPUT
- 3 DISPLAY:
-WAVESTAR
INFINITY
- 3 CONTROL CHASSIS:
-M4G
-CONTRACTOR BOARD
ENHANCED
-BCMS
- 3 MAIN INPUT

200% NEUTRAL
BUSBAR (RH & LH)



**SIDE VIEW
PANELS REMOVED**

CONDUIT
AREA



BOTTOM VIEW

- 7 RECOMMENDED INPUT CABLE SIZE: (3) 300MCM CU PER PHASE
- 6 APPROXIMATE WEIGHT: 6500 LBS
- 5 MINIMUM CLEARANCE FOR DOORS.
- 4 MINIMUM VENTILATION CLEARANCE FOR REAR
AND ONE SIDE OF UNIT.
- 3 ALL OPERATOR CONTROLS ARE FRONT ACCESS
WITHOUT EXPOSURE TO LIVE PARTS.
- 2 ALL ROUTINE MAINTENANCE IS FRONT AND SIDE ACCESS.
- 1 DIMENSIONS IN [] ARE MILLIMETER.

NOTES: UNLESS OTHERWISE SPECIFIED:

		THIRD ANGLE PROJECTION				THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED WRITTEN PERMISSION OF POWER DISTRIBUTION, INC.		
MATERIAL: N/A				DESCRIPTION: PDU 600KVA 1X1200A 6X400A				
APPROVALS		DATE		SIZE B	DWG. NO. 11300112SUB	REV X0		
DRAWN BY	AD	10/16/2019				SCALE:		
CHECKED BY	KN	10/16/2019				SHEET 1 OF 1		
APPROVED BY	MW	10/16/2019						