



NOTES:

1. OPERATOR INTERFACE PANEL.
2. MAIN INPUT CIRCUIT BREAKER.
3. 1000A I-LINE PANEL BOARD (HMA495SL10).
4. UP TO (8) 400A SUBFEEDS.
5. PM8?? SERIES METER TO MONITOR INPUT.
6. MINIMUM OF 36" CLEARANCE FOR DOOR SWING.
7. RECOMMEND 6" CLEARANCE BETWEEN VENTILATED SIDES AND WALL FOR PROPER COOLING.



TOP ENTRY/BOTTOM EXIT

THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION INC.		TITLE		-OUTLINE-		
		PDU (300 kVA) WITH RH 12" SIDECAR (FRONT ACCESS) 1000A I-LINE PANEL W/ SUB-FEEDS				
		DWG. NUMBER	SHEET 1 OF 1	REVISION		
		PDU18526		-A-		
DRAWN BY	RAE	CHECKED BY	LN			
DATE	06-04-15	DATE	06-04-15			



PDI
creating the perfect wave