




NOTES:

1. OPERATOR INTERFACE PANEL.
2. DUAL MAIN INPUT BREAKERS (WITH KIRK KEY).
3. SOLENOID KEY RELEASE.
4. (5) 225A SUB FEED BREAKERS.
5. (1) 60A SUB FEED BREAKER.
6. MINIMUM OF 36" CLEARANCE FOR DOOR SWING IN FRONT.
7. MINIMUM OF 36" CLEARANCE FOR DOOR SWING ON LEFT SIDE.
8. RECOMMEND A MINIMUM OF 30" IN REAR FOR MAINTENANCE.
9. RECOMMEND 6" CLEARANCE BETWEEN VENTILATED SIDES AND WALL FOR PROPER COOLING.



<p>THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION INC.</p>	TITLE		-OUTLINE-
	MDP POWERPAK PDU 200-300kVA (1) 60A & (5) 225A SUBFEEDS		
	DWG. NUMBER	SHEET 1 OF 1	REVISION
	MDP19144		-A-
DRAWN BY	RAE	CHECKED BY	MP
DATE	10-21-15	DATE	10-21-15



PDI
creating the perfect wave