



GENERAL NOTES:

1. ENCLOSURE: NEMA 1 RATED
2. ALL DOOR HAVE LOCKABLE HANDLE WITH COMMON KEY
3. ALL BUS IS SILVER-PLATED COPPER, BASED ON 1000A/ SQ IN.
4. WEIGHT :550 LBS.. ESTIMATED
5. OPERATING AMBIENT TEMPERATURE 0C TO 40C (32 F TO 104F)
6. HEAT DISSIPATION AT FULL RATE: 1 KW
7. FINISH: EXTERIOR PANELS: PEARL WHITE
8. RECOMMENDED MINIMUM CLEARANCE :FRONT: 36", SIDE : 6"
9. CABLE ENTRANCE AND EXIT THOUGH BOTTOM, PRE PUNCH 1/2" CONDUIT PLATE PROVIDED

FOR PROPOSAL ONLY
NOT FOR PRODUCTION

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [] IN MILLIMETER ANGULAR: ±0.5° BEND ±1° TWO PLACE DECIMAL ±0.02 THREE PLACE DECIMAL ±0.005		THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF SMITHS POWER		
THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING		
APPROVALS		DATE		TITLE: WALL MOUNT, 225A, MISSION CRITICAL (1) 225A NF PANEL BOARDS WITH BCMS
DRAWN LJN		7/30/15		
CHECKED				
ENG. APPR.				
SIZE		DWG. NO.		REV
B		RPP18744		A
		PART NO.		SHEET 1 OF 1