

Rigid/intermediate grade conduit fittings

90 Degree pull elbows

90 DEGREE PULL ELBOWS – MALLEABLE IRON

Features:

- Raintight
- Furnished with neoprene gasketed steel cover
- Furnished with steel locknut
- Furnished with stamped steel cover
- Threaded for rigid conduit and IMC
- For outdoor use
- Standard finish: zinc plated

Gasketed – rigid to box (male to female)

UL File No. E-19189



Cat. #	Size	Unit qty.	Wt. lbs. per 100
810	1/2"	20	34
811	3/4"	10	56
812	1"	5	88
813	1 1/4"	2	92
814	1 1/2"	2	200
815	2"	1	344

Rigid to rigid (female to female)

UL File No. E-19189



Cat. #	Size	Unit qty.	Wt. lbs. per 100
820	1/2"	20	36
821	3/4"	10	49
822	1"	5	94
823	1 1/4"	2	140
824	1 1/2"	2	200
825	2"	1	344

90 DEGREE PULL ELBOWS – ZINC DIE CAST

Applications:

- For connecting threaded rigid or IMC to form a 90° bend, or for connecting rigid or IMC to box or enclosure
- Removable cover and gasket facilitate wire pulling

Standard materials:

- Body – zinc
- Gasket – neoprene
- Cover – aluminum

Gasketed – rigid to box (male to female)

UL File No. E-19189



Cat. #	Size	Unit qty.	Wt. lbs. per 100
850RB DC	1/2"	20	17
875RB DC	3/4"	15	25
8100RB DC	1"	6	53
8125RB DC	1 1/4"	3	80

Rigid to rigid (female to female)

UL File No. E-19189



Cat. #	Size	Unit qty.	Wt. lbs. per 100
850RR DC	1/2"	20	15
875RR DC	3/4"	15	23
8100RR DC	1"	6	50
8125RR DC	1 1/4"	3	80

Combo emt – rigid/imc

UL File No. E-19189



Cat. #	Size	Unit qty.	Wt. lbs. per 100
850MT DC	1/2"	20	15
875MT DC	3/4"	15	23
8100MT DC	1"	6	50
8125MT DC	1 1/4"	3	80