

Gland type:

- Portable cord connector

Cable type:

- Non-armored

Features:

- Body well for Chico A sealing compound (contact factory)
- Standard neoprene seal suitable for use in operating temperatures -25°C to 40°C
- Available with NPT threads

Certifications and compliances:


- CSA certified Class I, Division 1, Groups C, D^A
- Class II, Divisions 1 & 2, Groups E, F, G
- Class III
- CSA File No. LR13046

Standard material and finishes:

- Body – steel with zinc electroplate and chromate finish coat
- Gland nut – aluminum



1G



Ordering information:

Entry thread size (A)			Outer sheath (E)		Gland length less entry (F)
NPT size	Cat. #	Form	Min.	Max.	
1/2"	CGBS1013	A	0.312	0.437	5.250
3/4"	CGBS2013	A	0.312	0.437	5.250
3/4"	CGBS2014	A	0.375	0.500	5.250
1"	CGBS3015	B	0.500	0.625	2.875
1"	CGBS3016	B	0.625	0.750	2.938
1 1/4"	CGBS4017	B	0.750	0.875	2.813
1 1/4"	CGBS4018	B	0.875	1.000	3.500
1 1/4"	CGBS4019	B	1.000	1.188	3.563

All dimensions in inches.

^AApplicable for Form B only.