

Condulet GUR conduit outlet boxes with covers

Cl. I, Div. 1 & 2, Groups C, D
 Cl. II, Div. 1, Groups E, F, G
 Cl. II, Div. 2, Groups F, G
 Cl. III
 NEMA 4

Explosionproof
 Dust-ignitionproof
 Raintight
 Wet Locations

3F
3F

Applications:

GUR conduit outlet boxes are installed within hazardous areas:

- To protect conductors in threaded rigid conduit
- To act as pull and splice boxes
- To connect lengths of conduit
- To provide access to conductors for maintenance and future system changes
- To change conduit direction
- Where space is limited, such as underneath gasoline pumps

Features:

GUR outlet boxes feature:

- Neoprene o-ring standard in cover to meet NEMA 4/UL Type 4 requirements
- Internal green ground screw #10
- Five standard hubs with three pipe plugs included
- Threaded cover opening
- Recesses in cover to assist in cover tightening and removal
- Smooth, integral hub bushing to protect conductor insulation when pulling
- Compact design for confined spaces
- UL and cUL Listed
- Optional all-aluminum construction

Certifications and compliances:

NEC/CEC:

- Class I, Divisions 1 & 2, Groups C, D
- Class II, Division 1, Groups E, F, G
- Class III
- Zones 1 & 2

UL standard:

- UL1203

CSA standard:

- cUL to CSA standard C22.2 No. 30

Environmental rating:

- NEMA 4

Standard materials:

- Bodies – Feraloy iron alloy
- Covers – copper-free aluminum

Standard finishes:

- Feraloy iron alloy – electrogalvanized with aluminum acrylic paint
- Aluminum – natural

Options:

- | Description | Suffix |
|---------------------------------------|-----------|
| • Bodies – copper-free aluminum | SA |

Accessories (ordered separately):

- | Description | Cat. # |
|---------------------------|-----------------|
| • Replacement gasket..... | GASK1801 |



Ordering information:

Hub size	Cat. #
1/2"	GUR1
3/4"	GUR2
1"	GUR3

Dimensions (in inches):

