


# Ceiling boxes

## 3 1/2" NON-METALLIC CEILING BOXES – PVC


2 7/8" DEEP

UL LISTED

Weight limit: 50 lbs. for fixture except where indicated.



TP16200,  
(TP16201 – 2 1/8" deep)  
old work



TP16201



TP16311

Cat. #	Clamps	Ground plate	Bracket/ bar hanger	Capacity cu. in.	No. of clamp openings	Fan rated (weight lbs.)	Fixture rated (weight lbs.)	Unit qty.	Wt. lbs. per 100
TP16200 <sup>B</sup>	Yes	-	Snap	15.0	4	No	14 (fixture) 6 (wall)	50	27
TP16201 <sup>B</sup>	Yes	Yes	Snap	15.0	4	No	14 (fixture) 6 (wall)	50	29
TP16311 <sup>A</sup>	Yes	Yes	Nails	18.0	4	No	50	75	20

<sup>A</sup>Nail bracket is set 1 1/16" back from the face of the box.

## 4" NON-METALLIC CEILING BOXES – PVC

2 1/4" DEEP

UL LISTED

Weight limit: 50 lbs. for fixture except where indicated.



TP16111, TP16110



TP16122, TP16123

Cat. #	Clamps	Ground plate	Bracket/ bar hanger	Capacity cu. in.	No. of clamp openings	Fan rated (weight lbs.)	Fixture rated (weight lbs.)	Unit qty.	Wt. lbs. per 100
TP16111	Yes	-	Nails	20.3	4	No	50	75	19
TP16110	Yes	Yes	Nails	20.0	4	No	50	75	21
TP16122	Yes	-	14" - 16"	20.8	4	No	50	20	59
TP16123	Yes	Yes	14" - 16"	20.8	4	No	50	20	61

# Ceiling boxes

## NON-METALLIC CEILING FAN BOXES

2<sup>3</sup>/<sub>16</sub>" DEEP

UL LISTED

With clamps for non-metallic cable.

All mounting hardware supplied; suitable for support of fans weighing up to 35 lbs.

### Features:

- Made of heavy duty, engineered thermoplastic material
- Offers the labor saving feature of quick entry and integral clamping
- Eliminates the need to use a screwdriver to break open pry-outs
- The easy access entry point serves as a wire clamp, eliminating time required to mechanically secure the wire to the box



TP16511

Cat. #	Diameter	Mounting method	Capacity cu. in.	No. Of clamp openings	Fan rated (weight lbs.)	Fixture rated (weight lbs.)	Unit qty.	Wt. lbs. per 100
TP16511	4"	Nails only	20.8	6	35	50	25	21

# Ceiling boxes

## CEILING FAN BOXES – PVC

### UL LISTED

Weight limits: fans and fixtures are supported independent of outlet box. Mounting screws go through box and into joist.

Box will support up to 70 lbs. for fans and 90 lbs. for fixtures. Provided with Romex connector.



TP1300

Cat. #	Description	Capacity cu. in.	Knockouts	Integral clamp	Fan rated (weight lbs.)	Fixture rated (weight lbs.)	Unit qty.	Wt. lbs. per 100
TP1300	4 <sup>1</sup> / <sub>16</sub> " dia., 1/2" deep pan section, 4" deep overall – with mounting hardware and external clamp, protective cover	14.0	3 - 1/2"	1	70	90	24	34