# **AC/MC** fittings

## Quick-Lok<sup>™</sup> connectors

### QUICK-LOK™ CONNECTORS - STEEL

#### **Features:**

- No locknut required
- Single unit or duplex construction with captive clamp
- Connects 50 MC, AC and flex RW cable sizes with just three fittings
- Easy to install: tilt, insert and snap down
- Single unit construction eliminates loose component parts; integral green plastic insulated throat bushing provides maximum protection for wire installation

## Standard material:

• Tubular steel

#### Standard finish:

• Zinc plated

UL File No. E-19188







#### Cable size

Cat. #	Trade size	HCF	Aluminum and steel RWFMC/FMC	Cable dia. range	Unit qty.	Wt. lbs. per 100
QLK50S <b>@</b>	¹/₂" single	14/2 to 10/3	3/8"	0.385" - 0.600"	50	8
QLK50D <b>2</b>	¹/₂" duplex	14/2 to 10/3	1/2"	0.433" - 0.600"	25	10
QLK75 <b>Ø①</b>	3/4"	10/3 to 6/3	3/8" & 1/2"	0.550" - 0.850"	25	14

**Q**UL approved for use with aluminum interlocking grounding metal-clad cable, Type MCIA (Southwire MCAP\*\*).

MCAP<sup>™</sup> is a registered trademark of Southwire company.

1 UL approved for use with MC-PCS cable.

