

AC/MC fittings

Quick-Lok™ Pro connectors – zinc die cast & steel

QUICK-LOK™ PRO CONNECTORS – ZINC DIE CAST & STEEL

Applications:

- Quick-Lok™ Pro connectors are used to connect armored cable, metal-clad cable, MCI-A cable, MC-PCS cable or flexible metallic conduit to a box or enclosure for dry location applications
- Fits 1/2" knockout

Connectors:

- **Single connector** – For installation of one cable into a box or enclosure
- **Duplex connector** – Allows for installation of two cables in a single KO, into box or enclosure
- **90° connector** – For installation of 90° bend in cable
- **Old work connector** – For installing and terminating cable after an old work box has been installed

Features:

- Easy tool-free installation (the single and old work connector can also be removed without tools)
- Integral insulated throat bushing provides protection for wire insulation
- Reusable
- Wide range of styles and configurations to meet customer requirements and preferences
- Single unit construction eliminates loose component parts
- Duplex and 90° connector cover opens wide for easy access and wiring
- For use in dry locations/concrete tight when taped

Certifications and compliances:

- cULus
- UL File No. E-19188
- Concrete tight when taped

Standard materials:

- Body – zinc die cast, zinc plated steel
- Cover – zinc plated steel
- Insulator – non-metallic



Cable size

Cat. #	Description	Cable size			Cable dia. range	Outlet box KO size	Unit qty.	Wt. lbs. per 100
		AL and steel AC	AL and steel MC/MCI-A/ MC-PCS/HCF ²	AL and steel RWFMC				
38MCQ	3/8" Connector	14/2 to 10/3	14/2 to 10/3	3/8"	0.395" - 0.638"	1/2"	50	6.0
38MCQS	3/8" Connector	14/2 to 10/3	14/2 to 10/3	3/8"	0.395" - 0.638"	1/2"	50	6.0
38MCQSBUCKET	3/8" Connector	14/2 to 10/3	14/2 to 10/3	3/8"	0.395" - 0.638"	1/2"	1 ²	43 ²
38MCQBULK	3/8" Connector	14/2 to 10/3	14/2 to 10/3	3/8"	0.395" - 0.638"	1/2"	500	6.0
38MCQD	3/8" Duplex connector - zinc	14/2 to 10/3	14/2 to 10/3	3/8"	0.460" - 0.610"	1/2"	25	11.3
38MCQDS	3/8" Duplex connector - steel	14/2 to 10/3	14/2 to 10/3	3/8"	0.460" - 0.610"	1/2"	25	11.3
38MCQDBULK	3/8" Duplex connector	14/2 to 10/3	14/2 to 10/3	3/8"	0.460" - 0.610"	1/2"	250	11.3
38MCQ90	3/8" 90° connector	14/2 to 10/3	14/2 to 10/4	3/8"	0.469" - 0.610"	1/2"	25	7.5
50MCQ90	1/2" 90° connector	8/2 to 8/3	8/2 to 8/3	1/2"	0.670" - 0.785"	1/2"	25	11.3
38MCQOW	3/8" Old work connector	14/2 to 10/3	14/2 to 10/3	-	0.395" - 0.638"	1/2"	50	6.0

² UL approved for use with aluminum interlocking grounding metal-clad cable, Type MCIA (Southwire MCAP™).

MCAP™ is a registered trademark of Southwire company.

² Unit quantity and weight listed is per bucket. One bucket consists of 700 connectors and one pallet consists of 24 buckets. Pallet quantity is 16,800 which consists of two layers of 12 buckets per layer.