






| NPT | ISO |   | N/m |
|--------|------|---|------|
| 1/8" | M10 | | 6,5 |
| 1/4" | M12 | | 7,5 |
| 3/8" | M16 | | 12,5 |
| 1/2" | M20 | | 20 |
| 3/4" | M25 | | 30 |
| 1" | M32 | | 55 |
| 1" 1/4 | M40 | | 75 |
| 1" 1/2 | M50 | | 100 |
| 2" | M63 | | 135 |
| 2" 1/2 | M75 | | 175 |
| 3" | M90 | | 300 |
| 3" 1/2 | M100 | | 400 |
| 4" | M110 | | 480 |

| ADE | N° |  B (mm) |   | N/m |
|-----|----|--|--|------|
| | 3 | 2,75 - 5,5 | | 6,5 |
| | 4 | 4,5 - 8,5 | | 7,5 |
| | 5 | 7 - 12 | | 12,5 |
| | 6 | 10 - 16 | | 20 |
| | 7 | 13,5 - 21 | | 30 |
| | 8 | 18 - 27,5 | | 55 |
| | 9 | 23 - 34 | | 75 |
| | 10 | 29 - 41 | | 100 |
| | 11 | 35 - 48 | | 135 |
| | 12 | 42 - 56 | | 175 |
| | 13 | 50 - 65 | | 240 |
| | 14 | 58 - 74 | | 300 |
| | 15 | 66 - 83 | | 400 |
| | 16 | 75 - 93 | | 480 |
| | 17 | 85 - 104 | | 610 |

