


Reducing rings

Technical specifications

- Material: PVC, perbunan
- Compliance with cable glands: ECP- ISOCAP- NORMADIX- NEWCAP



PVC reducing ring - for ECP- ISOCAP- NORMADIX

SIZE	FOR CABLE GLAND		CABLE Ø		STANDARD ORDER UNIT	CATALOG NUMBER
	ISO	Pg	MIN	MAX		
5	M16	Pg9	3.5	6.5	100	CAP240735
6	M16bis	Pg11	5.5	8.7	100	CAP240935
7	M20	Pg13	5.5	8.7	100	CAP241235
7	M20	Pg13	7.0	10.5	100	CAP241135
8	M20bis	Pg16	5.5	8.7	100	CAP241535
8	M20bis	Pg16	7.0	10.5	100	CAP241435
8	M20bis	Pg16	8.0	12.5	100	CAP241335
9	M25	Pg21	10.0	15.0	100	CAP241635
10	M32	Pg29	14.0	19.0	50	CAP242135
11	M40	Pg36	17.5	25.0	10	CAP242935
12	M50	Pg42	22.0	32.5	20	CAP242635
13	M63	Pg48	22.0	32.5	20	CAP244735
13	M63	Pg48	26.0	38.0	20	CAP244235



Perbunan reducing ring - for NEWCAP

GLAND SIZE	CABLE DIAMETER		ORDER UNIT	CATALOG NUMBER
	MIN	MAX		
5/4	3.0	6.5	100	CAP180504
6/5	4.5	10.0	100	CAP180605
7/6	6.0	13.0	100	CAP180706
8/7	10.0	18.0	100	CAP180807
9/8	16.0	24.0	100	CAP180908
10/9	22.0	32.0	100	CAP181009
11/10	29.0	40.5	100	CAP181110
12/11	37.0	53.0	100	CAP181211

All dimensions in mm.