

10 x 85 mm 1500 V d.c. Photovoltaic fuse links



Product description

Eaton's Bussmann® series 10 x 85 mm fuse links are specifically designed to protect photovoltaic strings.

Features

- Compatible with Eaton's Bussmann series CHPV15L85 fuse holder (see data sheet 10628).
- IEC and UL Accreditations

Catalogue symbol

- PV-(Amps)A10F85L for example PV-15A10F85L

Technical data

- Rated voltage: 1500 V d.c.
- Rated current: 2.25, 2.5, 3, 3.5, 4, 5, 12, 15, 16, 20, 25 and 30 A
- Breaking capacity: 30 kA d.c. 1 ms
- Class of operation: gPV

Standards/Approvals

- IEC 60269
- UL 248-19
- RoHS compliant


Packaging

- MOQ: 10


Table 1. Technical Data

Catalogue numbers	Rated current (A)	Rated voltage (V d.c.)	Energy integrals I ² t (A ² s)		Watts loss (W)	
			Pre-arcing	Total at 1500 V d.c.	0.8 I _n	I _n
PV-2.25A10F85L	2.25	1500	3	10	1.4	2.4
PV-2.5A10F85L	2.5	1500	4	10	1.3	2.1
PV-3A10F85L	3	1500	7	20	1.3	2.2
PV-3.5A10F85L	3.5	1500	10	20	1.6	2.6
PV-4A10F85L	4	1500	15	30	1.7	2.8
PV-5A10F85L	5	1500	33	60	1.7	2.8
PV-12A10F85L	12	1500	19	240	2.1	3.5
PV-15A10F85L	15	1500	42	300	2.2	3.6
PV-16A10F85L	16	1500	48	350	2.1	3.5
PV-20A10F85L	20	1500	108	800	2.7	4.5
PV-25A10F85L	25	1500	190	1400	3.4	5.6
PV-30A10F85L	30	1500	485	3500	4	6.6

Dimensions - mm



Time-current curve



Changes to the products, to the information contained in this document, and to prices are reserved; so are errors and omissions. Only order confirmations and technical documentation by Eaton is binding. Photos and pictures also do not warrant a specific layout or functionality. Their use in whatever form is subject to prior approval by Eaton. The same applies to Trademarks (especially Eaton, Moeller, and Cutler-Hammer). The Terms and Conditions of Eaton apply, as referenced on Eaton Internet pages and Eaton order confirmations.

Eaton Electrical Products Limited
 Melton Road
 Burton-on-the-Wolds
 LE12 5TH, United Kingdom
 www.eaton.com

© 2018 Eaton
 All Rights Reserved
 PDF Only
 Publication No. 10658
 June 2019