

# DOOR MOUNTING FOR UL508 DISCONNECT SWITCHES

**SWITCH REF.**

<b>16A to 40A</b>	<b>63A to 80A</b>
RD16-3-508	RD63-3-508
RD25-3-508	RD80-3-508
RD40-3-508	

3.15 in / 80 mm

3.15 in / 80 mm

⚠ Switch must be turned  
L'interrupteur doit être retourné

**STEP 1**

DOOR-508

Dual dimensions / Double dimensions / Doble dimensiones

in/mm / in/mm / in/mm

13.3 lb-in / 1,5 Nm / Pozidriv 2

OR / OU

13.3 lb-in / 1,5 Nm

0.03 to 0.15 in / 0,8 à 3 mm

90°

ON

OFF

Type 1, 3R, 4, 4X, 12

⓪-O-OFF

**STEP 2**

⓪-O-OFF

Click!

2

1

**STEP 3**

Click!

2

1

CONFIGURATION	
SWITCH	Position
RD16-3-508 - RD25-3-508 RD40-3-508 - RD63-3-508 - RD80-3-508	1
RD16-3-508 + POLE-16 RD25-3-508 + POLE-25 RD40-3-508 + POLE-40	2

1

2

Click!

**⚠ DANGER** / **⚠ PELIGRO** / **⚠ TENSION ALTA**

**⚠ PELIGRO VOLTAGE** This equipment may be subject to TENSION ALTA (Voltage) conditions. Only qualified personnel should install and service this equipment. Turn off all power before working on or inside equipment. Before working on or inside equipment, disconnect the power supply and lock out the power source. Verify that the power is off before working on or inside equipment. Failure to follow these instructions may result in death or serious injury.

**⚠ TENSION ALTA** Este equipo puede estar sujeto a condiciones de TENSION ALTA (Voltaje). Solo personal cualificado debe instalar y prestar servicios de mantenimiento a este equipo. Desconecte el equipo antes de realizar trabajos de mantenimiento o dentro del equipo. Antes de trabajar en o dentro del equipo, desconecte el suministro de energía y bloquee la fuente de alimentación. Verifique que la alimentación está apagada antes de trabajar en o dentro del equipo. El incumplimiento de estas instrucciones puede resultar en la muerte o lesiones graves.



541576A