

NDNF1-WH

Specifications

Description: Fuse holding rail mount terminal block.

Circuit Jumper: JF1,
2 circuits

Fuse Size: $1\frac{3}{32}$ " X $1\frac{1}{2}$ "*
(KTK, FNQ).

Poles: 1

Wire Range: AWG #8-22 Cu.

Ratings:

Volts: — 600V

Amps: — 30A

Mounting Options: 35mm DIN rail, C-rail

Fuse Pullers: • PF1 (standard)
• neon or incandescent bulb

*LPF1 (lighted neon or incandescent bulb).

Torque Rating: 18 lb-in

Operating Temperature: 105°C

Agency Information: CSA File 15364

Catalog Numbers

Catalog

Number	Color
--------	-------

NDNF1-WH	White
----------	-------

Fuse Pullers (Optional): PF1

Lighted neon or incandescent lamp:

Catalog

Numbers	Voltage
---------	---------

LPF1-24	24
---------	----

LPF1-120	120
----------	-----

LPF1-120-C	120
------------	-----

LPF1-220	220
----------	-----

LPF1-440	440
----------	-----

