



Utvalgsguide effektbryter NZM1



Powering Business Worldwide

Effektbryter NZM1 3-polt

Komplet effektbryter 15...160 A I henhold til EN 60497 I_2 = høyeste prøvestrøm = $1,3 \times I_n$ I_i = elektromagnetisk utløserstrøm A-type: termisk/elektromagnetisk vern	Ik max: Ics = Icu = 30 kA (230 V) Rammeklemme for 70 mm ² (2 x 25 mm ²) Cu B x H x D = 90 x 145 x 85 mm	Ik max: Ics = Icu = 80 kA (230 V) Rammeklemme for 70 mm ² (2 x 25 mm ²) Cu B x H x D = 90 x 145 x 85 mm		
	3-polet NZMB1-...	3-polet NZMN1-...		
Beskrivelse	Type	Elnr	Type	Elnr
Effektbryter Ir: 15 - 20 A li: 350 A	NZMB1-A20	4359030	NZMN1-A20	4358979
Effektbryter Ir: 20 - 25 A li: 350 A	NZMB1-A25	4358976	NZMN1-A25	4358980
Effektbryter Ir: 25 - 32 A li: 350 A	NZMB1-A32	4358977	NZMN1-A32	4358981
Effektbryter Ir: 32 - 40 A li: 320-400 A	NZMB1-A40	4358700	NZMN1-A40	4358706
Effektbryter Ir: 40 - 50 A li: 300-500 A	NZMB1-A50	4358701	NZMN1-A50	4358707
Effektbryter Ir: 50 - 63 A li: 380-630 A	NZMB1-A63	4358702	NZMN1-A63	4358708
Effektbryter Ir: 63 - 80 A li: 480-800 A	NZMB1-A80	4358703	NZMN1-A80	4358709
Effektbryter Ir: 80 - 100 A li: 600-1000 A	NZMB1-A100	4358704	NZMN1-A100	4358710
Effektbryter Ir: 100 - 125 A li: 750 - 1250 A	NZMB1-A125	4358705	NZMN1-A125	4358711
Effektbryter Ir: 125 - 160 A li: 1280A	NZMB1-A160	4358978	NZMN1-A160	4358982



Tilleggsutstyr

Avdekninger og tilkobling

NZM1 16-95 mm ² Al/Cu	NZM1-XKA	4358881	NZM1-XKA	4358881
NZM1 Multiklemme 6x16 mm ² Cu	NZM1-XKAM	4358623	NZM1-XKAM	4358623
Boltsett 3 stk	NZM1-XKS	4358733	NZM1-XKS	4358733
Avdekning IP20	NZM1-XKSA	4358738	NZM1-XKSA	4358738
IP2X for rammeklemme	NZM1-XIPK	4358883	NZM1-XIPK	4358883
IP2X avdekning	NZM1-XIPA	4358885	NZM1-XIPA	4358885



Annet tilbehør

Vrigrep på bryter, låsbart, sort	NZM1-XDV	4358727	NZM1-XDV	4358727
Mekanisk forrigling 1 pr bryter	NZM1-XMV	4359007	NZM1-XMV	4359007
Wire til mekanisk forrigling 90-225 mm	NZM-XBZ225	4359004	NZM-XBZ225	4359004
Wire til mekanisk forrigling 225-600 mm	NZM-XBZ600	4359005	NZM-XBZ600	4359005
Wire til mekanisk forrigling 600-1000 mm	NZM-XBZ1000	4359006	NZM-XBZ1000	4359006
Dørgrep, låsbart, sort u/ aksselforlenger	NZM1-XTVD	4358728	NZM1-XTVD	4358728
Dørgrep, låsbart, rød u/ aksselforlenger	NZM1-XTVDVR	4358729	NZM1-XTVDVR	4358729
Aksselforlenger 270 mm	NZM1/2-XV4	4358731	NZM1/2-XV4	4358731
Dørgrep, låsbart, sort lav høyde	NZM1-XTVDV-0	4358970	NZM1-XTVDV-0	4358970
Dørgrep, låsbart, rød lav høyde	NZM1-XTVDVR-0	4358969	NZM1-XTVDVR-0	4358969
Hjelpekontakt NC	M22-K01	4355364	M22-K01	4355364
Hjelpekontakt NO	M22-K10	4355363	M22-K10	4355363
Underspenningsutløser 230 V	NZM1-XUL208-240AC	4358719	NZM1-XUL208-240AC	4358719
Arbeidsstrømsutløser 230 V	NZM1-XAL208-250AC/DC	4358726	NZM1-XAL208-250AC/DC	4358726
Feste for DIN-skinne	NZM1-XC35	4358742	NZM1-XC35	4358742
Låsebøyle	NZM1-XKAV	4358739	NZM1-XKAV	4358739



Effektbryter NZM1 4-polt

Komplet effektbryter 15...160 A I henhold til EN 60497 I_2 = høyeste prøvestrøm = 1,3 x I_n I_i = elektromagnetisk utløserstrøm A-type: termisk/elektromagnetisk vern	Ik max: Ics = Icu = 25 kA (400 V) Rammeklemme for 70 mm ² (2 x 25 mm ²) Cu B x H x D = 125 x 145 x 85 mm 100 % vern i nøytral	Ik max: Ics = Icu = 50 kA (400 V) Rammeklemme for 70 mm ² (2 x 25 mm ²) Cu B x H x D = 125 x 145 x 85 mm 100 % vern i nøytral		
	4-polet NZMB1-...	4-polet NZMN1-...		
Beskrivelse	Type	Elnr	Type	Elnr
Effektbryter Ir: 15 - 20 A li: 350 A	NZMB1-4-A20	4358983	NZMN1-4-A20	4358987
Effektbryter Ir: 20 - 25 A li: 350 A	NZMB1-4-A25	4358984	NZMN1-4-A25	4358988
Effektbryter Ir: 25 - 32 A li: 350 A	NZMB1-4-A32	4358985	NZMN1-4-A32	4358989
Effektbryter Ir: 32 - 40 A li: 320-400 A	NZMB1-4-A40	4358815	NZMN1-4-A40	4358821
Effektbryter Ir: 40 - 50 A li: 300-500 A	NZMB1-4-A50	4358816	NZMN1-4-A50	4358822
Effektbryter Ir: 50 - 63 A li: 380-630 A	NZMB1-4-A63	4358817	NZMN1-4-A63	4358823
Effektbryter Ir: 63 - 80 A li: 480-800 A	NZMB1-4-A80	4358818	NZMN1-4-A80	4358824
Effektbryter Ir: 80 - 100 A li: 600-1000 A	NZMB1-4-A100	4358819	NZMN1-4-A100	4358825
Effektbryter Ir: 100 - 125 A li: 750 - 1250 A	NZMB1-4-A125	4358820	NZMN1-4-A125	4358826
Effektbryter Ir: 125 - 160 A li: 1280A	NZMB1-4-A160	4358986	NZMN1-4-A160	4358990



Tilleggsutstyr

Avdekninger og tilkobling

NZM1 16-95 mm ² Al/Cu	NZM1-4-XKA	4358882	NZM1-4-XKA	4358882
NZM1 Multiklemme 6x16 mm ² Cu	NZM1-4-XKAM	4358625	NZM1-4-XKAM	4358625
Boltsett 4 stk	NZM1-4-XKS	4358895	NZM1-4-XKS	4358895
Avdekning IP20	NZM1-4-XKSA	4358880	NZM1-4-XKSA	4358880
IP2X for rammeklemme	NZM1-4-XIPK	4358884	NZM1-4-XIPK	4358884
IP2X for avdekning	NZM1-4-XIPA	4358886	NZM1-4-XIPA	4358886



Annet tilbehør

Vrigrep på bryter, låsbart, sort	NZM1-XDV	4358727	NZM1-XDV	4358727
Mekanisk forrigling 1 pr bryter	NZM1-XMV	4359007	NZM1-XMV	4359007
Wire til mekanisk forrigling 90-225 mm	NZM-XBZ225	4359004	NZM-XBZ225	4359004
Wire til mekanisk forrigling 225-600 mm	NZM-XBZ600	4359005	NZM-XBZ600	4359005
Wire til mekanisk forrigling 600-1000 mm	NZM-XBZ1000	4359006	NZM-XBZ1000	4359006
Dørgrep, låsbart, sort u/ akselforlenger	NZM1-XTVD	4358728	NZM1-XTVD	4358728
Dørgrep, låsbart, rødt u/ akselforlenger	NZM1-XTVDVR	4358729	NZM1-XTVDVR	4358729
Akselforlenger 270 mm	NZM1/2-XV4	4358731	NZM1/2-XV4	4358731
Dørgrep, låsbart, sort lav høyde	NZM1-XTVDV-0	4358970	NZM1-XTVDV-0	4358970
Dørgrep, låsbart, rødt lav høyde	NZM1-XTVDVR-0	4358969	NZM1-XTVDVR-0	4358969
Hjelpekontakt NC	M22-K01	4355364	M22-K01	4355364
Hjelpekontakt NO	M22-K10	4355363	M22-K10	4355363
Underspenningsutløser 230 V	NZM1-XUL208-240AC	4358719	NZM1-XUL208-240AC	4358719
Arbeidsstrømsutløser 230 V	NZM1-XAL208-250AC/DC	4358726	NZM1-XAL208-250AC/DC	4358726
Feste for DIN-skinne	NZM1-XC35	4358742	NZM1-XC35	4358742
Låsebøyle	NZM1-XKAV	4358739	NZM1-XKAV	4358739



Eaton's electrical business is a global leader with deep regional application expertise in power distribution and circuit protection; power quality, backup power and energy storage; control and automation; life safety and security; structural solutions; and harsh and hazardous environment solutions. Through end-to-end services, channel and an integrated digital platform & insights Eaton is powering what matters across industries and around the world, helping customers solve their most critical electrical power management challenges.

For more information, visit [Eaton.com](https://www.eaton.com).



Eaton Electric
AS Ryensvingen 5-7
0680 Oslo, Norge

Eaton
EMEA Headquarters
Route de la Longeraie 7
1110 Morges, Switzerland
[Eaton.com](https://www.eaton.com)

© 2023 Eaton
All Rights Reserved
Publication No. SA012023NN
April 2023

Changes to the products, to the information contained in this document, and to prices are reserved; so are errors and omissions. Only order confirmations and technical documentation by Eaton is binding. Photos and pictures also do not warrant a specific layout or functionality. Their use in whatever form is subject to prior approval by Eaton. The same applies to Trademarks (especially Eaton, Moeller, and Cutler-Hammer). The Terms and Conditions of Eaton apply, as referenced on Eaton Internet pages and Eaton order confirmations.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

