



# Utvalgsguide effektbryter NZM3



*Powering Business Worldwide*

# Effektbryter digital NZM3

Komplette effektbryter 100...630 A Iht EN 60497 VX-type = elektronisk forinket vern PX-type = elektronisk forinket vern med display og energimåling lsd = forinket elektromagnetisk utløserstrøm li = elektromagnetisk utløserstrøm T = Terra, A = ARMS, Z = Soneselektivitet	<b>Ik max: lcs = lcu = 85 kA (230 V)</b> Bolttilkobling på bryteren B x H x D = 140 x 275 x 166 mm	<b>Ik max: lcs = lcu = 50 kA (400 V)</b> Bolttilkobling på bryteren B x H x D = 185 x 275 x 166 mm VAR - Justerbar null-leder (0-60-100%)
	<b>3-polet NZMN3-...</b>	<b>4-polet NZMN3-...</b>

Beskrivelse	Type	Elnr	Type	Elnr
Effektbryter lr: 100-250A lsd: 2 -10 li: 2 -18 LSI	NZMN3-VX250	4362685		
Effektbryter lr: 160-400A lsd: 2 -10 li: 2 -12 LSI	NZMN3-VX400	4362691	NZMN3-4-VX400/VAR	4362728
Effektbryter lr: 252-630A lsd: 1,5 -7 li: 2 -8 LSI	NZMN3-VX630	4362722	NZMN3-4-VX630/VAR	4362807
Effektbryter lr: 100-250A lsd: 2 -10 li: 2 -18 LSIG	NZMN3-VX250-T	4362697		
Effektbryter lr: 160-400A lsd: 2 -10 li: 2 -12 LSIG	NZMN3-VX400-T	4362707	NZMN3-4-VX400-T	4362776
Effektbryter lr: 252-630A lsd: 1,5 -7 li: 2 -8 LSIG	NZMN3-VX630-T	4362770	NZMN3-4-VX630-T	4362887
Effektbryter lr: 100-250A lsd: 2 -10 li: 2 -18 LSI	NZMN3-PX250	4362718	NZMN3-4-PX250/VAR	4362804
Effektbryter lr: 160-400A lsd: 2 -10 li: 2 -12 LSI	NZMN3-PX400	4362745	NZMN3-4-PX400/VAR	4362831
Effektbryter lr: 252-630A lsd: 1,5 -7 li: 2 -8 LSI	NZMN3-PX630	4362825	NZMN3-4-PX630/VAR	4362929
Effektbryter lr: 100-250A lsd: 2 -10 li: 2 -18 LSIG	NZMN3-PX250-TAZ	4362802	NZMN3-4-PX250/VAR-TAZ	4362912
Effektbryter lr: 160-400A lsd: 2 -10 li: 2 -12 LSIG	NZMN3-PX400-TAZ	4362826	NZMN3-4-PX400/VAR-TAZ	4362928
Effektbryter lr: 252-630A lsd: 1,5 -7 li: 2 -8 LSIG	NZMN3-PX630-TAZ	4362923	NZMN3-4-PX630/VAR-TAZ	4362964

## Tilleggsutstyr

### Avdekninger og tilkobling

Al/Cu-klemmer 16-240 mm <sup>2</sup> med avdekning < 350 A	NZM3-XKA1	4358873	NZM3-4-XKA1	4358875
Al/Cu-klemmer 2x 50-240 mm <sup>2</sup> med avdekning	NZM3-XKA2	4358874	NZM3-4-XKA2	4358876
IP20 Lang avdekning	NZM3-XKSA	4358809	NZM2-4-XKS	4358896
IP2X Kort avdekning	NZM3-XKSAE	4359068	NZM3-XKSAE	4359068
IP2X for rammeklemme	NZM3-XIPK	4358891	NZM3-4-XIPK	4358892
IP2X for lang avdekning	NZM3-XIPA	4358893	NZM3-4-XIPA	4358894
Rammeklemme 35-240 mm <sup>2</sup> Cu	NZM3-XKC	4358805	NZM3-4-XKSAE	4359070

### Annet tilbehør

Strømforsyning, en-fas, 100-240 VAC/24 VDC, 2,5 A	PSG60E24RM	4560889	PSG60E24RM	4560889
Modbusmodul RTU for NZM PXR	PXR-RCAM-MRTU-I	4362642	PXR-RCAM-MRTU-I	4362642
Relè-modul	NZM2/3-X2A	4363017	NZM2/3-X2A	4363017
Underspenningsspole for AX/VX - 230 VAC	NZM2/3-XU208-240AC	4358767	NZM2/3-XU208-240AC	4358767
Underspenningsspole for PX - 230 VAC	NZM2/3-XU2A208-240AC	4363014	NZM2/3-XU2A208-240AC	4363014
Arbeidstrømsutløser for AX/VX - 230 VAC	NZM2/3-XA208-250AC/DC	4358771	NZM2/3-XA208-250AC/DC	4358771
Arbeidstrømsutløser for PX - 230 VAC	NZM2/3-XA2A208-240AC	4363009	NZM2/3-XA2A208-240AC	4363009
Kommunikasjonsmodul for PXR, RJ45, EtherCAT	PXR-ECAM-ECT	4363162	PXR-ECAM-ECT	4363162
Kommunikasjonsmodul for PXR, RJ45, Ethernet/IP	PXR-ECAM-IP	4363163	PXR-ECAM-IP	4363163
Kommunikasjonsmodul for PXR, RJ45, ProfiNet	PXR-ECAM-PNET	4363164	PXR-ECAM-PNET	4363164
Interfacemodul for kommunikasjon til VX-brytere	NZM3-XBSM	4362676	NZM3-XBSM	4362676
Motordrift 230 VAC	NZM3-XR208-240AC	4358803	NZM3-XR208-240AC	4358803
Avdekning 4pol ved motordrift			NZM3-XAVPR	4359017

**Eaton Electric**  
 AS Ryensvingen 5-7  
 0680 Oslo, Norge

**Eaton**  
 EMEA Headquarters  
 Route de la Longeraie 7  
 1110 Morges, Switzerland  
 Eaton.com

© 2023 Eaton  
 All Rights Reserved  
 Publication No. SA012025NN  
 July 2023

Changes to the products, to the information contained in this document, and to prices are reserved; so are errors and omissions. Only order confirmations and technical documentation by Eaton is binding. Photos and pictures also do not warrant a specific layout or functionality. Their use in whatever form is subject to prior approval by Eaton. The same applies to Trademarks (especially Eaton, Moeller, and Cutler-Hammer). The Terms and Conditions of Eaton apply, as referenced on Eaton Internet pages and Eaton order confirmations.

Eaton is a registered trademark.  
 All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

