



83 mm (3.3")

90 mm (3.5")

83 mm (3.3")

5.5 mm (0.22")

X, Y

OBEN

1

2

3

80 mm (3.1")

90 mm (3.5")

80 mm (3.1")

NZM3 ≥ 230 mm (9")

NZM4 ≥ 290 mm (11.5")

a

4

5

229 mm (9")

	l
2 mm ≤ a < 4.5 mm (0.08" ≤ a ≤ 0.18")	9.5 mm (0.37")
4.5 mm ≤ a ≤ 6 mm (0.18" ≤ a ≤ 0.24")	13 mm (0.51")

RTR-NZM10

05/15 IL012060ZU
AWA 123-1211

Emergency On Call Service: Local representative
(www.eaton.eu/aftersales) or +49 (0) 180 5 223822 (de, en)

All Rights Reserved

Eaton Industries GmbH, Hein-Moeller-Straße 7-11, 53115 Bonn, Germany
© 1992 by Eaton Industries GmbH, www.eaton.eu/documentation

EATON
Powering Business Worldwide

235 mm (9.3")

Printed in Germany (04/15) Doku