EM2802 Series EuroMag Terminal Blocks

30° Entry; Screwless; 2.54 Centers

SPECIFICATIONS

Rating: 4A, 150V

Center Spacing: 0.10" (2.54mm) Wire Range: #20-28 AWG

Housing Material: Gray Polyamide Type 6/6, 94V0

Contact Material: Tin-Plated Brass Spring Material: Stainless Steel

Operating Temperature: 105°C (221°F) max., -40°C

(-40°F) min.

Recommended PCB Hole Diameters: 0.051" (1.30mm)

Construction: Mold-to-Length

Agency Information: Plus File E62622; CE Certified




EM280207

Dimensions - mm (in)	Dim	ensions	- mm	ı (in)
----------------------	-----	---------	------	--------

Poles	L (mm)
2 3 4 5 6 7 8 9 10 11	7.08 9.62 12.16 14.70 17.24 19.78 22.32 24.86 27.40 29.94 32.48

To convert to inches, divide by 25.4



Part Numbering System

Series # of Poles

EM2802

02 to **12**