

Product Change Notice

PCN#: EE-PCN17007

01/27/2017

CLASSIFICATION OF CHANGE:

End of Life (EOL)

DESCRIPTION OF CHANGE:

Various configurations within the Single Row barrier strip product line has reached EOL.

REASON FOR CHANGE:

Due low sales volume over the last two years, these configurations will no longer be offered.

EXPECTED INFLUENCE ON QUALITY, RELIABILITY, AND PERFORMANCE:

Not applicable.

PARTS FAMILIES AFFECTED:

See table on next page

TIME SCHEDULE:

Last Time Buy Date: February 28, 2017

Last Time Shipment Date: April 30,2017

SAMPLE AVAILABILITY:

No samples available

QUALIFICATION DATA:

Not applicable

ISSUED BY:

Nick Stone

Product Manager

CONTACT INFORMATION:

For questions or comments, please contact your local [Eaton sales representative](#).

Part Series	Obsolete Option
A5000	Terminal Style: 04 - Wire Wrap Tail
A1000	Terminal Style: 03 non feed-thru
	Terminal Bending: R45
	Screw Option: CA - Standard Captive Screw
	Pole Configuration: 25-36 Poles
A2000/LP2000	Option: MT - Mounting Plate
	Option: RC - Retaining Clip
	Terminal Bending: R30
	Terminal Bending: R36
	Terminal Bending: R39
	Terminal Bending: R48
	Terminal Bending: R69
	Terminal Bending: R77
	Pole Configuration: 27-32 Poles Mount End Base; 29-32 Poles Barrier End Base
A3000/LP3000	Option: SO - Standoff
	Option: S1 - Solder Lug
	Terminal Bending: R30
	Terminal Bending: R35
	Terminal Bending: R39
	Terminal Bending: R48
	Terminal Bending: R53
	Terminal Bending: R63
	Terminal Bending: R69
	Terminal Bending: R75
	Terminal Bending: R77
	Option: DR - Drilled Right Angle
	CB3000
Pole Configuration: 22-28 Poles Barrier End Base; 20-26 Poles Mount End Base	

Part Series	Obsolete Option
B38	Terminal Style: 2 - Short Turret
A4000/B4000	Terminal Style: 80 - Screw Top, Stud Bottom
	Option: CW - Cup Washer
	Pole Configuration: 17-18 Pole
	Option: S1 - Solder Lug
CB5000	Terminal Style: 01 - Handwired
	Pole Configuration: 28-30 Poles
CB1000	Terminal Style: EB - Exit Back
	Pole Configuration: 31-36 Poles
	Screw Option: 03CA - Stainless Captive
	Screw Option: 07CA - Steel SEMS Captive
CB2000	Option: MT Mounting Plate
	Screw Option: 07CA - Steel SEMS Captive
	Pole Configuration: 27-32 Barrier End Base; 25-30 Mount End Base
A38	Screw Option: 94 - Brass, Ni-Plated Slotted