

Product Change Notice

PCN#: EE-PCN16046

12/22/2016

CLASSIFICATION OF CHANGE:

Polymer PTC Resettable Fuse (PPTC)

DESCRIPTION OF CHANGE:

The carton dimension change including inner and outer

REASON FOR CHANGE:

In order to optimize the utilization of packaging material

EXPECTED INFLUENCE ON QUALITY, RELIABILITY, AND PERFORMANCE:

There will be no effect on the quality, reliability, or performance. There are no changes to form, fit, and function of the devices.

PARTS FAMILIES AFFECTED:

Please refer to below

TIME SCHEDULE:

Start Shipment Date: 2016/10/16

SAMPLE AVAILABILITY:

N/A

QUALIFICATION DATA:

N/A

ISSUED BY:

Global Product Manager: Matt Joiner

Product Manager: Wayne Wang

CONTACT INFORMATION:

For questions or comments, please contact your local [Eaton sales representative](#).

Eaton P/N	SPQ	Outside Carton					
		Size		Quantity			
		(mm)		Bag / Outside Carton		pcs/ Outside Carton	
		Before	After	Before	After	Before	After
PTS08059V010	4000	350*265*270	350*350*300	20	28	80000	112000
PTS080524V010	4000	350*265*270	350*350*300	20	28	80000	112000
PTS08059V020	4000	350*265*270	350*350*300	20	28	80000	112000
PTS08056V035	4000	350*265*270	350*350*300	20	28	80000	112000
PTS08056V050	4000	350*265*270	350*350*300	20	28	80000	112000
PTS08056V075	4000	350*265*270	350*350*300	20	28	80000	112000
PTS120660V005	2500	350*265*270	350*350*300	20	28	50000	70000
PTS120660V010	2500	350*265*270	350*350*300	20	28	50000	70000
PTS120630V012	5000	350*265*270	350*350*300	20	28	100000	140000
PTS120630V016	5000	350*265*270	350*350*300	20	28	100000	140000
PTS120624V020	5000	350*265*270	350*350*300	20	28	100000	140000
PTS120616V025	5000	350*265*270	350*350*300	20	28	100000	140000
PTS120616V035	5000	350*265*270	350*350*300	20	28	100000	140000
PTS12066V050	5000	350*265*270	350*350*300	20	28	100000	140000
PTS120615V050	2500	350*265*270	350*350*300	20	28	50000	70000
PTS12066V075	5000	350*265*270	350*350*300	20	28	100000	140000
PTS12066V100	2500	350*265*270	350*350*300	20	28	50000	70000
PTS12066V110	2500	350*265*270	350*350*300	20	28	50000	70000
PTS12066V150	2500	350*265*270	350*350*300	20	28	50000	70000
PTS12066V200	2500	350*265*270	350*350*300	20	28	50000	70000
PTS181230V010	1000	350*265*270	350*350*300	18	24	18000	24000
PTS181260V014	1000	350*265*270	350*350*300	18	24	18000	24000
PTS181230V020	1000	350*265*270	350*350*300	18	24	18000	24000
PTS181216V035	2000	350*265*270	350*350*300	18	24	36000	48000
PTS181216V050	2000	350*265*270	350*350*300	18	24	36000	48000
PTS181213V075	2000	350*265*270	350*350*300	18	24	36000	48000
PTS181224V075	1000	350*265*270	350*350*300	18	24	18000	24000
PTS181233V075	1000	350*265*270	350*350*300	18	24	18000	24000
PTS18128V110	2000	350*265*270	350*350*300	18	24	36000	48000
PTS181216V110	1000	350*265*270	350*350*300	18	24	18000	24000
PTS181224V110	1000	350*265*270	350*350*300	18	24	18000	24000
PTS181233V110	1000	350*265*270	350*350*300	18	24	18000	24000
PTS18126V125	2000	350*265*270	350*350*300	18	24	36000	48000
PTS181216V125	1000	350*265*270	350*350*300	18	24	18000	24000
PTS18128V150	2000	350*265*270	350*350*300	18	24	36000	48000
PTS181212V150	1000	350*265*270	350*350*300	18	24	18000	24000
PTS181224V150	1000	350*265*270	350*350*300	18	24	18000	24000

PTS18128V160	2000	350*265*270	350*350*300	18	24	36000	48000
PTS18128V200	2000	350*265*270	350*350*300	18	24	36000	48000
PTS18126V260	1000	350*265*270	350*350*300	18	24	18000	24000
PTS18126V300	1000	350*265*270	350*350*300	18	24	18000	24000

Eaton P/N	SPQ	Inner Box		Outside Carton					
		Size		Size		Quantity			
		(mm)		(mm)		Reel/ Outside Carton		pcs/ Outside Carton	
		Before	After	Before	After	Before	After	Before	After
PTR016V0090-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR016V0110-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR016V0135-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR016V0160-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR016V0185-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR016V0250-TR(1)	2500	350*350*75	Cancel	380*380*340	350*350*300	4	5	10000	12500
PTR016V0300-TR(1)	2500	350*350*75	Cancel	380*380*340	350*350*300	4	5	10000	12500
PTR016V0400-TR(1)	2500	350*350*75	Cancel	380*380*340	350*350*300	4	5	10000	12500
PTR016V0500-TR(1)	1500	350*350*75	Cancel	380*380*340	350*350*300	4	5	6000	7500
PTR016V0600-TR(1)	1500	350*350*75	Cancel	380*380*340	350*350*300	4	5	6000	7500
PTR016V0700-TR(1)	1500	350*350*75	Cancel	380*380*340	350*350*300	4	5	6000	7500
PTR016V0800-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	5	4000	5000
PTR016V0900-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR016V1000-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR016V1100-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR016V1200-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR016V1300-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR016V1400-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR016V1500-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR030V0090-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR030V0110-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR030V0135-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR030V0160-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR030V0185-TR(1)	2000	350*350*75	Cancel	380*380*340	350*350*300	4	5	8000	10000
PTR030V0250-TR(1)	2000	350*350*75	Cancel	380*380*340	350*350*300	4	5	8000	10000
PTR030V0300-TR(1)	2000	350*350*75	Cancel	380*380*340	350*350*300	4	5	8000	10000
PTR030V0400-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	5	4000	5000
PTR030V0500-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR030V0600-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR030V0700-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR030V0800-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000

PTR030V0900-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR060V0010-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR060V0017-TR(1)	2500	350*350*75	Cancel	380*380*340	350*350*300	4	5	10000	12500
PTR060V0020-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR060V0025-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR060V0030-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR060V0040-TR(1)	3000	350*350*75	Cancel	380*380*340	350*350*300	4	5	12000	15000
PTR060V0050-TR(1)	2000	350*350*75	Cancel	380*380*340	350*350*300	4	5	8000	10000
PTR060V0065-TR(1)	2000	350*350*75	Cancel	380*380*340	350*350*300	4	5	8000	10000
PTR060V0075-TR(1)	2000	350*350*75	Cancel	380*380*340	350*350*300	4	5	8000	10000
PTR060V0090-TR(1)	2000	350*350*75	Cancel	380*380*340	350*350*300	4	5	8000	10000
PTR060V0110-TR(1)	1500	350*350*75	Cancel	380*380*340	350*350*300	4	5	6000	7500
PTR060V0135-TR(1)	1500	350*350*75	Cancel	380*380*340	350*350*300	4	5	6000	7500
PTR060V0160-TR(1)	1500	350*350*75	Cancel	380*380*340	350*350*300	4	5	6000	7500
PTR060V0185-TR(1)	1500	350*350*75	Cancel	380*380*340	350*350*300	4	5	6000	7500
PTR060V0250-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR060V0300-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000
PTR060V0375-TR(1)	1000	350*350*75	Cancel	380*380*340	350*350*300	4	4	4000	4000

Eaton P/N	SPQ	Small White Box				Outside Carton					
		Size		Quantity		Size		Quantity			
		(mm)		pcs/ Box		(mm)		Box/ Outside Carton		pcs/ Outside Carton	
		Before	After	Before	After	Before	After	Before	After	Before	After
PTR016V0090-BK(1)	1000	160*120*60	160*160*65	2000	2000	350*265*270	350*350*300	16	16	32000	32000
PTR016V0110-BK(1)	1000	160*120*60	160*160*65	2000	2000	350*265*270	350*350*300	16	16	32000	32000
PTR016V0135-BK(1)	1000	160*120*60	160*160*65	2000	2000	350*265*270	350*350*300	16	16	32000	32000
PTR016V0160-BK(1)	1000	160*120*60	160*160*65	2000	2000	350*265*270	350*350*300	16	16	32000	32000
PTR016V0185-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR016V0250-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR016V0300-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR016V0400-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR016V0500-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR016V0600-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR016V0700-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR016V0800-BK(1)	500	240*165*60	160*160*65	1000	1000	350*265*270	350*350*300	8	16	8000	16000
PTR016V0900-BK(1)	500	240*165*60	160*160*65	1000	1000	350*265*270	350*350*300	8	16	8000	16000
PTR016V1000-BK(1)	250	240*165*60	160*160*65	500	500	350*265*270	350*350*300	8	16	4000	8000
PTR016V1100-BK(1)	250	240*165*60	160*160*65	500	500	350*265*270	350*350*300	8	16	4000	8000

PTR016V1200-BK(1)	250	240*165*60	160*160*65	500	500	350*265*270	350*350*300	8	16	4000	8000
PTR016V1300-BK(1)	250	240*165*60	160*160*65	500	250	350*265*270	350*350*300	8	16	4000	4000
PTR016V1400-BK(1)	250	240*165*60	160*160*65	500	250	350*265*270	350*350*300	8	16	4000	4000
PTR016V1500-BK(1)	250	240*165*60	160*160*65	500	250	350*265*270	350*350*300	8	16	4000	4000
PTR030V0090-BK(1)	1000	160*120*60	160*160*65	2000	2000	350*265*270	350*350*300	16	16	32000	32000
PTR030V0110-BK(1)	1000	160*120*60	160*160*65	2000	2000	350*265*270	350*350*300	16	16	32000	32000
PTR030V0135-BK(1)	1000	160*120*60	160*160*65	2000	2000	350*265*270	350*350*300	16	16	32000	32000
PTR030V0160-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR030V0185-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR030V0250-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR030V0300-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR030V0400-BK(1)	500	240*165*60	160*160*65	1000	1000	350*265*270	350*350*300	8	16	8000	16000
PTR030V0500-BK(1)	500	240*165*60	160*160*65	1000	500	350*265*270	350*350*300	8	16	8000	8000
PTR030V0600-BK(1)	500	240*165*60	160*160*65	1000	500	350*265*270	350*350*300	8	16	8000	8000
PTR030V0700-BK(1)	250	240*165*60	160*160*65	500	500	350*265*270	350*350*300	8	16	4000	8000
PTR030V0800-BK(1)	250	240*165*60	160*160*65	500	250	350*265*270	350*350*300	8	16	4000	4000
PTR030V0900-BK(1)	250	240*165*60	160*160*65	500	250	350*265*270	350*350*300	8	16	4000	4000
PTR060V0010-BK(1)	1000	160*120*60	160*160*65	2000	2000	350*265*270	350*350*300	16	16	32000	32000
PTR060V0017-BK(1)	1000	160*120*60	160*160*65	2000	2000	350*265*270	350*350*300	16	16	32000	32000
PTR060V0020-BK(1)	1000	160*120*60	160*160*65	2000	2000	350*265*270	350*350*300	16	16	32000	32000
PTR060V0025-BK(1)	1000	160*120*60	160*160*65	2000	2000	350*265*270	350*350*300	16	16	32000	32000
PTR060V0030-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR060V0040-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR060V0050-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR060V0065-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR060V0075-BK(1)	500	160*120*60	160*160*65	1000	1000	350*265*270	350*350*300	16	16	16000	16000
PTR060V0090-BK(1)	500	240*165*60	160*160*65	1000	1000	350*265*270	350*350*300	8	16	8000	16000
PTR060V0110-BK(1)	500	240*165*60	160*160*65	1000	1000	350*265*270	350*350*300	8	16	8000	16000
PTR060V0135-BK(1)	500	240*165*60	160*160*65	1000	1000	350*265*270	350*350*300	8	16	8000	16000
PTR060V0160-BK(1)	500	240*165*60	160*160*65	1000	500	350*265*270	350*350*300	8	16	8000	8000
PTR060V0185-BK(1)	500	240*165*60	160*160*65	1000	500	350*265*270	350*350*300	8	16	8000	8000
PTR060V0250-BK(1)	250	240*165*60	160*160*65	500	500	350*265*270	350*350*300	8	16	4000	8000
PTR060V0300-BK(1)	250	240*165*60	160*160*65	500	250	350*265*270	350*350*300	8	16	4000	4000
PTR060V0375-BK(1)	250	240*165*60	160*160*65	500	250	350*265*270	350*350*300	8	16	4000	4000