



NEMA Type 4/4X multi-door enclosure



NEMA Type 4X two-door enclosure

Large ground mounted enclosure line extension

Quality • Performance • Aesthetics

We have expanded our large enclosure offering to include both multi-door freestanding and disconnect ready enclosures in both NEMA Type 4 and 4X options.

Manufactured in Sherman, Texas, our enclosures provide reliable electrical equipment protection for variable frequency drives, motors, controls, electrical devices and other power distribution equipment.

Key features

- Single, double and multi-door options
- NEMA 4 (Carbon Steel) and NEMA 4X (304 Stainless Steel) options
- Full line of accessories: thermal management, panels, locks, latches, lights, and many others
- UL Listed for U.S. and Canada to UL508 and CSA C22.2 standards

NEMA Type 4 and 4X Freestanding Multi-door

- Size range from 112" to 187" wide
- Three styles of enclosure construction
 - Three-door: Single and double door
 - Four-door: (2) Double door sections
 - Five-door: Single and (2) double door sections

NEMA 4 and 4X Disconnect Ready

- **Floorstanding**
 - Double door
 - Flange and center mount disconnect location options
 - Sizes range from 60" to 72" tall by 48" to 73" wide
- **Freestanding**
 - Flange mount disconnect location
 - One to five door option
 - Sizes range from 72" to 90" tall by 27" to 196" wide

Reference B-Line series enclosures product catalog for sizes, models, ratings, accessories, materials, finishes and additional services.

Contact us at 800-851-7415

EATON

Powering Business Worldwide

Eaton.com/ENC

Quality • Performance • Aesthetics

Large enclosures you want when you need them



NEMA 4/4X Freestanding Multi-door

NEMA 4	NEMA 4X	H	W	D
8611214-4FS	8611214-4XSFS	86	112	14
8615014-4FS	8615014-4XSFS	86	150	14
8618714-4FS	8618714-4XSFS	86	187	14



Floor Standing Center Disconnect

NEMA 4	NEMA 4X	H	W	D
CD604812-4FD	CD604812-4XSFD	60	48	12
CD606012-4FD	CD606012-4XSFD	60	60	12
CD726012-4FD	CD726012-4XSFD	72	60	12
CD727212-4FD	CD727212-4XSFD	72	72	12
CD727218-4FD	CD727218-4XSFD	72	72	18



Freestanding Disconnect

NEMA 4	NEMA 4X	H	W	D
FD722718-4FS	FD722718-4XSFS	72	27	18
FD723318-4FS	FD723318-4XSFS	72	33	18
FD723918-4FS	FD723918-4XSFS	72	39	18
FD843918-4FS	FD843918-4XSFS	84	39	18
FD903920-4FS	FD903920-4XSFS	90	39	20
FD903924-4FS	FD903924-4XSFS	90	39	24
FD725318-4FS	FD725318-4XSFS	72	53	18
FD726518-4FS	FD726518-4XSFS	72	65	18
FD727718-4FS	FD727718-4XSFS	72	77	18
FD727724-4FS	FD727724-4XSFS	72	77	24
FD847718-4FS	FD847718-4XSFS	84	77	18
FD907720-4FS	FD907720-4XSFS	90	77	20
FD907724-4FS	FD907724-4XSFS	90	77	24
FD729918-4FS	FD729918-4XSFS	72	99	18
FD8411718-4FS	FD8411718-4XSFS	84	117	18
FD9011724-4FS	FD9011724-4XSFS	90	117	24
FD8415718-4FS	FD8415718-4XSFS	84	157	18
FD8419618-4FS	FD8419618-4XSFS	84	196	18



Floor Standing Flange Disconnect

NEMA 4	NEMA 4X	H	W	D
FD604912-4FD	FD604912-4XSFD	60	49	12
FD606112-4FD	FD606112-4XSFD	60	61	12
FD726112-4FD	FD726112-4XSFD	72	61	12
FD727312-4FD	FD727312-4XSFD	72	73	12
FD604918-4FD	FD604918-4XSFD	60	49	18
FD606118-4FD	FD606118-4XSFD	60	61	18
FD726118-4FD	FD726118-4XSFD	72	61	18
FD727318-4FD	FD727318-4XSFD	72	73	18
FD727324-4FD	FD727324-4XSFD	72	73	24

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2022 Eaton
All Rights Reserved
Printed in USA
Publication No. SA304018EN
September 2022



Powering Business Worldwide

B-Line Division
509 West Monroe Street
Highland, IL 62249
United States
Phone: 800-851-7415
Eaton.com/enc

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.

Eaton.com/ENC

Follow us on social media to get the
latest product and support information.

