

Bag Nomenclature Chart

All the information necessary to understand an Eaton filter bag description is listed below. The filter description listed, is a PO-10-P04S-H-20, a polypropylene, 10 micron, plain no cover, 4"x15" filter bag with a carbon steel ring, a twill handle packed 20 to a box.

Type of Material	
LOF-CLEAR® - ACCUGAF® - PROGAF®	
Multi-layer meltblown polypropylene media	
HAYFLOW® & DURAGAF®	
PEXLF	Extended life polyester, no scrim, glazed
PEXL	Extended life polyester, no scrim, glazed
POXLF	Extended life polypropylene, no scrim, g
POXL	Extended life polypropylene, no scrim, g
UNIRING® - Fully Welded	
PEU	Polyester needled felt. Singed.
POU	Polypropylene needled felt. Singed.
SENTINEL® - Fully Welded	
PE	Polyester needled felt. Singed.
PEF	Polyester FDA compliant felt.
PO	Polypropylene needled felt. Singed.
POF	Polypropylene FDA compliant felt.
SNAP RING® & BANDSEAL™	
PE	Polyester needled felt. Singed.
PO	Polypropylene needled felt. Singed.
N	Nylon needled felt. PE scrim
HT	Nomex needled felt with scrim
PT	Teflon® needled felt. PE scrim
NMO	Nylon monofilament mesh
PEMO	Polyester monofilament mesh
PMO	Polypropylene monofilament mesh
PTMO	Teflon® monofilament mesh
PEMU	Polyester multifilament mesh

Micron Rating
1
5
10
25
50
75
100
200

Cover Type	
PEMU 150	A
Extruded Mesh Cover & PO Spun Bond (4	E
NIMO 80	N
Plain (No Cover)	P
PE Spun Bonded Cover (AGF Only)	R
Modified/Special	M

Size	
Short 7" Bag 7 x 16"	1
Long 7" Bag 7 x 32"	2
Long Modified	02M
Short 4" Bag 4 x 8"	3
Long 4" Bag 4 x 14"	4
Special	99

Ring Type	
SNAP RINGS	
A	Stainless steel snap ring
B	Nylon snap ring
O	Polypropylene snap ring
S	Carbon steel snap ring, Zinc Plated
UNIRING® Rings	
UE	Polypropylene UNIRING®
UK	Kopel UNIRING®
SENTINEL Rings	
E	Polypropylene SENTINEL® Ring
H	Polyester SENTINEL® ring
Z	Santoprene SENTINEL® ring
Tie-on Bag (No Ring)	
R	Tie-on Bag (no ring)
Other Ring Types	
M	Modified / Special

Options	
C	Reverse collar
E	Twill tape reinforced side and thread other than standard
F	Thread other than standard
H	1 Handle in Twill tape
K	Round flat bottom (bucket shape)
L	Standard bag with increased length
M	Special
N	Mesh bag without a felt collar
P	Packaging without plastic liner
Q	Other than standard label
T	Mesh bag with twill tape collar
U	Turned inside out
W	Welded side and bottom only
WW	Fully welded
Y	Side welded/sewn bottom & ring

Bags per Box
4 to 100

