



NOTES:

1. ALL DIMENSIONS ARE IN INCHES [MM].
2. DESIGN DATA:

DESIGN PRESSURE- 125 PSIG [8.6 BARS]
 DESIGN TEMPERATURE- 450° F [232.2 °C]
 MIN. DESIGN METAL TEMP.- -20° F @ 125 PSIG
 [-28.9° C @ 8.6 BARS]

3. MATERIAL: BODY & COVER - CAST IRON, SA-278 CLASS 30
INTERNALS - STAINLESS STEEL
4. PART NO.: 230-ACN
5. APPROX. WEIGHT: 25 LBS. [11.3 KG.]

CERTIFIED FOR:

P.O. NO.:
 S.O. NO.:
 QUOTE NO.:
 TAG NO.:



EATON FILTRATION, LLC
 900 FAIRMOUNT AVENUE, ELIZABETH, NEW JERSEY 07207

NAME TYPE 230-ACN FLOAT DRAIN TRAP
 FOR COMPRESSED AIR & GAS SERVICE
 CAST IRON

SIZE	DWG NO	DATE	CERT.	VAA	DATE	REV
A	FM	6/3/04		VAA	6/3/04	C

ELECTRONIC FILE NAME: SD230ACN.DWG
 REF. ECR D507 DATE 10/18/05

UNAUTHORIZED USE, MANUFACTURE OR
 REPRODUCTION IN WHOLE OR IN PART IS
 PROHIBITED. DRAWING, DESIGN AND
 OTHER DISCLOSURES PROPERTY OF
 EATON FILTRATION, LLC

SD230ACN