



DIMENSIONS						
PIPE SIZE (NOMINAL)	CLASS 150		CLASS 300		CLASS 600	
	A		A		B	
	IN.	MM	IN.	MM	IN.	MM
1" (25mm)	2.38	/ 60	2.38	/ 60	0.81	/ 21
1-1/2" (40mm)	3.13	/ 80	3.13	/ 80	1.38	/ 35
2" (50mm)	3.88	/ 99	3.88	/ 99	1.75	/ 44
2-1/2" (65mm)	4.63	/ 118	4.63	/ 118	2.25	/ 57
3" (80mm)	5.13	/ 130	5.13	/ 130	2.75	/ 70
4" (100mm)	6.63	/ 168	6.63	/ 168	3.50	/ 89
5" (125mm)	7.50	/ 191	7.50	/ 191	4.63	/ 118
6" (150mm)	8.50	/ 216	8.50	/ 216	5.50	/ 140
8" (200mm)	10.75	/ 273	10.75	/ 273	7.13	/ 181
10" (250mm)	13.13	/ 334	13.13	/ 334	9.00	/ 229
12" (300mm)	15.88	/ 403	15.88	/ 403	10.88	/ 276
14" (350mm)	17.50	/ 445	17.50	/ 445	12.63	/ 321
16" (400mm)	20.00	/ 508	20.00	/ 508	14.50	/ 368
18" (450mm)	21.38	/ 543	21.38	/ 543	16.38	/ 416
20" (500mm)	23.63	/ 600	23.63	/ 600	18.38	/ 467
24" (600mm)	28.00	/ 711	28.00	/ 711	22.38	/ 568

CERTIFIED FOR:
P.O. NO.:
REG. NO.:
QUOTE NO.:
MATERIAL:
TAG NO.:

EATON	EATON FILTRATION, LLC		
	900 FAIRMOUNT AVENUE, ELIZABETH, NEW JERSEY 07207		
NAME		MODEL 92 STRAINER BASKET CONE TYPE	
DRAWN	DM	DATE	10/14/97
CERT.	FM	DATE	10/14/97
SIZE	DWG	SD092CT	
A	NO	REV B	

ELECTRONIC FILE NAME: SD092CT.DWG
REF. ECR D507 DATE 11/1/05

UNAUTHORIZED USE, MANUFACTURE OR REPRODUCTION IN WHOLE OR IN PART IS PROHIBITED. DRAWING, DESIGN AND OTHER DISCLOSURES PROPERTY OF EATON FILTRATION, LLC