

## Cleaning and Disinfecting SIHA® Sterile Spray

**Spray disinfection of corks, filling valves and filling tubes, drain fittings, and any other accessible winery machine parts. Non-corrosive. SIHA Sterile Spray does not attack metals, rubber or plastic, with the exception of plexiglas. Immediately effective against molds, yeasts and bacteria.**



### Safety Notes and Recommendations:

H225, H319

P210, P233, P241, P243, P280.60, P337+313, P403+235

**Highly flammable liquid and vapour. Keep container tightly closed. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.**

### Application

- Screw sprayer tightly onto SIHA Sterile Spray bottle. Spray parts or surfaces to be disinfected from a distance of 8 – 12 in (20 – 30 cm). Ensure that a uniform film is generated.
- If the parts or surfaces to be treated are damp or wet, repeat application after approximately one minute.
- Repeat application approximately hourly and after breaks.

### Safety

When used and handled correctly, there are no known unfavorable effects associated with SIHA Sterile Spray.

Further safety information can be found in the relevant Material Safety Data Sheet, which can be downloaded from our website.

### Storage

SIHA Sterile Spray should be stored in a cool and locked place.

### Delivery Information

SIHA Sterile Spray is sold under article no. 78.231 and is available in the following package sizes:

0.26 gal (1 l) PE bottle

1.32 gal (5 l) PE canister

Packaging group II UN Nr. 1170

Storage class 3A (conforming concept VCI 09/93)

### Certified Quality

SIHA Sterile Spray is regularly laboratory tested according to technical functionality criteria in order to ensure consistently high product quality.

**North America**

44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

**Europe/Africa/Middle East**

Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0

Friedensstraße 41  
68804 Altlußheim, Germany  
Tel: +49 6205 2094-0

An den Nahewiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0

**China**

No. 3, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

**Singapore**

4 Loyang Lane #04-01/02  
Singapore 508914  
Tel: +65 6825-1668

**Brazil**

Rua Clark, 2061 - Macuco  
13279-400 - Valinhos, Brazil  
Tel: +55 11 3616-8400

**For more information, please  
email us at [filtration@eaton.com](mailto:filtration@eaton.com)  
or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)**

EN  
1 B 7.5.3  
03-2017

© 2016 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.



*Powering Business Worldwide*