

Applications:

- Berth and mirror
- Marine interior
- State room
- Head

Features:

- Compact design
- Adjustable shade
- Two-pole switch and convenience outlet provided

Certifications and compliances:

- UL1598A – Luminaires for Marine Vessels
- Conforms to IP40
- Marine Outside Type Saltwater
- ABS

Standard materials and finishes:

- Housing and shade – Type 5052H32 aluminum with an electrostatically applied polyester powder coat white high gloss finish
- End caps – white polycarbonate
- Lamp holder – porcelain

Technical specifications:

- Entries – three 1/2" knockouts
- Lamp holder – medium base
- Lamp type – A-19 60 watt maximum or self-ballasted compact fluorescent (lamp not provided)
- Convenience outlet – 125V, 2-pole, 3-wire U-ground; no convenience outlet (optional)
- Switch – 2-pole, rocker type
- Voltage – rated to operate up to 250 VAC, 60 Hz

Mounting option:

- Wall mount, through luminaire interior

Options:

Description	Suffix
• Without convenience outlet	LCO

Photometrics:

- Complete photometrics can be found at www.crouse-hinds.com/photometrics



Ordering information:

Cat. #	Description	Lamp size	Weight (lbs.)
1060A	Incandescent berth/mirror	A-19 60W max.	1.5

Accessories (ordered separately):

Cat. #	Description
INX3526	Lamp, 60W, A-19, incandescent
INX4087	Lamp holder, porcelain
CX3001	Convenience outlet, 15A, 125V
INX3379	Two-pole rocker switch

Dimensions (in inches):

