



Over 170 approved models!

Eaton's Crouse-Hinds has the most comprehensive listing of DLC approved products for hazardous and industrial areas.

About DesignLights Consortium®

DesignLights Consortium (DLC) is a collaboration of utility companies and regional energy efficiency organizations in the U.S. and Canada committed to ensuring that high quality, energy-efficient lighting design becomes commonplace in all commercial lighting installations.

DLC Qualified Products List

- Customers use the Qualified Products List (QPL) for guidance in selecting the most high quality, high performance, tested and verified LED products for specific applications
- Utility program administrators approve all LED brands listed in the QPL for their regional energy efficiency incentive and rebate programs
- The specification guidelines and procedures for getting listed on QPL are developed through a collaboration between DOE, ENERGY STAR members, the DLC committee and manufacturers
- See www.designlights.org for complete listing



Over
45

Utility companies and energy consortiums across the U.S. and Canada are DLC members.



Powering Business Worldwide

Eaton's Crouse-Hinds **DLC** approved products

Champ® VMV and Champ Pro PVM (3L-25L)



3L - 11L



13L & 17L



21L & 25L

Indoor

Part number*
[VMV/PVM]5L/[UNV1/UNV34]
[VMV/PVM]5LR1/[UNV1/UNV34]
[VMV/PVM]5LR3/[UNV1/UNV34]
[VMV/PVM]7L/[UNV1/UNV34]
[VMV/PVM]7LR1/[UNV1/UNV34]
[VMV/PVM]7LR3/[UNV1/UNV34]
[VMV/PVM]9L/[UNV1/UNV34]
[VMV/PVM]9LR1/[UNV1/UNV34]
[VMV/PVM]9LR3/[UNV1/UNV34]
[VMV/PVM]13L/UNV1
[VMV/PVM]13LR1/UNV1
[VMV/PVM]17L/UNV1
[VMV/PVM]17LR1/UNV1
[VMV/PVM]21L/UNV1
[VMV/PVM]21LR1/UNV1
[VMV/PVM]25L/UNV1

Outdoor

Part number*
[VMV/PVM]3L/[UNV1/UNV34]
[VMV/PVM]3LR1/[UNV1/UNV34]
[VMV/PVM]3LR3/[UNV1/UNV34]
[VMV/PVM]5L/[UNV1/UNV34]
[VMV/PVM]5LR1/[UNV1/UNV34]
[VMV/PVM]5LR3/[UNV1/UNV34]
[VMV/PVM]7L/[UNV1/UNV34]
[VMV/PVM]7LR1/[UNV1/UNV34]
[VMV/PVM]7LR3/[UNV1/UNV34]
[VMV/PVM]9L/[UNV1/UNV34]
[VMV/PVM]9LR1/[UNV1/UNV34]
[VMV/PVM]9LR3/[UNV1/UNV34]
[VMV/PVM]11L/[UNV1/UNV34]
[VMV/PVM]11LR3/[UNV1/UNV34]
[VMV/PVM]13L/UNV1

Part number*
[VMV/PVM]13LR1/UNV1
[VMV/PVM]13LR3/UNV1
[VMV/PVM]17L/UNV1
[VMV/PVM]17LR1/[UNV1/UNV34]
[VMV/PVM]17LR3/[UNV1/UNV34]
[VMV/PVM]21L/UNV1
[VMV/PVM]21LR1/UNV1
[VMV/PVM]21LR3/UNV1
[VMV/PVM]25L/UNV1
[VMV/PVM]25LR1/UNV1

* For text within brackets, choose one or the other to complete part number (i.e. VMV or PVM).

Champ® PLL, Champ MLL and Pauluhn™ DLL (2 & 4 ft.)



DLL, MLL, PLL 2 ft.



DLL, MLL, PLL 4 ft.

Indoor

Part number*
[DLL/PLL]2/UNV1 S903
[DLL/PLL]2/UNV1 S903D
[DLL/PLL]2N/UNV1 S903
[DLL/PLL]2N/UNV1 S903D
[DLL/PLL]4/UNV1 S903
[DLL/PLL]4/UNV1 S903D
[DLL/PLL]4N/UNV1 S903
[DLL/PLL]4N/UNV1 S903D

* For text within brackets, choose one or the other to complete part number (i.e. DLL, PLL or MLL).

All finishes approved.

Outdoor

Part number*
MLL2/[UNV1/UNV34]
MLL2/[UNV1/UNV34] S903
MLL2/[UNV1/UNV34] S903D
MLL2/[UNV1/UNV34] S891
MLL2N/[UNV1/UNV34]
MLL2N/[UNV1/UNV34] S903
MLL2N/[UNV1/UNV34] S903D
MLL2N/[UNV1/UNV34] S891
MLL4/[UNV1/UNV34]
MLL4/[UNV1/UNV34] S903
MLL4/[UNV1/UNV34] S903D
MLL4/[UNV1/UNV34] S891
MLL4N/[UNV1/UNV34]
MLL4N/[UNV1/UNV34] S903
MLL4N/[UNV1/UNV34] S903D
MLL4N/[UNV1/UNV34] S891

Eaton's Crouse-Hinds **DLC** approved products

Champ® FMV and Champ Pro PFM (3L-25L)



3L-25L

Indoor

Part number*

[FMV/PFM]5LCY/[UNV1/UNV34] D 76
[FMV/PFM]5LCY/[UNV1/UNV34] 76
[FMV/PFM]7LCY/[UNV1/UNV34] 76
[FMV/PFM]7LCY/[UNV1/UNV34] 76 S903
[FMV/PFM]7LCY/[UNV1/UNV34] 33
[FMV/PFM]7LCY/[UNV1/UNV34] 33 S903
[FMV/PFM]7LCY/[UNV1/UNV34] D 76
[FMV/PFM]7LCY/[UNV1/UNV34] D 76 S903
[FMV/PFM]7LCY/[UNV1/UNV34] D 33
[FMV/PFM]7LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]9LCY/[UNV1/UNV34] 76
[FMV/PFM]9LCY/[UNV1/UNV34] 76 S903
[FMV/PFM]9LCY/[UNV1/UNV34] 33
[FMV/PFM]9LCY/[UNV1/UNV34] 33 S903

Part number*

[FMV/PFM]9LCY/[UNV1/UNV34] D 76
[FMV/PFM]9LCY/[UNV1/UNV34] D 76 S903
[FMV/PFM]9LCY/[UNV1/UNV34] D 33
[FMV/PFM]9LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]11LCY/[UNV1/UNV34] 76
[FMV/PFM]11LCY/[UNV1/UNV34] 76 S903
[FMV/PFM]11LCY/[UNV1/UNV34] 33
[FMV/PFM]11LCY/[UNV1/UNV34] 33 S903
[FMV/PFM]11LCY/[UNV1/UNV34] D 76
[FMV/PFM]11LCY/[UNV1/UNV34] D 76 S903
[FMV/PFM]11LCY/[UNV1/UNV34] D 33
[FMV/PFM]11LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]13LCY/[UNV1/UNV34] 76
[FMV/PFM]13LCY/[UNV1/UNV34] 76 S903

Part number*

[FMV/PFM]13LCY/[UNV1/UNV34] 33
[FMV/PFM]13LCY/[UNV1/UNV34] 33 S903
[FMV/PFM]13LCY/[UNV1/UNV34] D 76
[FMV/PFM]13LCY/[UNV1/UNV34] D 76 S903
[FMV/PFM]13LCY/[UNV1/UNV34] D 33
[FMV/PFM]13LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]15LCY/[UNV1/UNV34] 33
[FMV/PFM]15LCY/[UNV1/UNV34] 33 S903
[FMV/PFM]15LCY/[UNV1/UNV34] 76
[FMV/PFM]15LCY/[UNV1/UNV34] 76 S903
[FMV/PFM]15LCY/[UNV1/UNV34] D 33
[FMV/PFM]15LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]15LCY/[UNV1/UNV34] D 76
[FMV/PFM]15LCY/[UNV1/UNV34] D 76 S903

Outdoor

Part number*

[FMV/PFM]3LCY/[UNV1/UNV34] 76
[FMV/PFM]3LCY/[UNV1/UNV34] 76 S891
[FMV/PFM]3LCY/[UNV1/UNV34] 76 S903
[FMV/PFM]3LCY/[UNV1/UNV34] 33
[FMV/PFM]3LCY/[UNV1/UNV34] 33 S891
[FMV/PFM]3LCY/[UNV1/UNV34] 33 S903
[FMV/PFM]3LCY/[UNV1/UNV34] D 76
[FMV/PFM]3LCY/[UNV1/UNV34] D 76 S891
[FMV/PFM]3LCY/[UNV1/UNV34] D 76 S903
[FMV/PFM]3LCY/[UNV1/UNV34] D 33
[FMV/PFM]3LCY/[UNV1/UNV34] D 33 S891
[FMV/PFM]3LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]5LCY/[UNV1/UNV34] 76
[FMV/PFM]5LCY/[UNV1/UNV34] 76 S891
[FMV/PFM]5LCY/[UNV1/UNV34] 76 S903
[FMV/PFM]5LCY/[UNV1/UNV34] D 33
[FMV/PFM]5LCY/[UNV1/UNV34] D 33 S891
[FMV/PFM]5LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]5LCY/[UNV1/UNV34] D 76
[FMV/PFM]5LCY/[UNV1/UNV34] D 76 S891
[FMV/PFM]5LCY/[UNV1/UNV34] D 76 S903

Part number*

[FMV/PFM]5LCY/[UNV1/UNV34] D 76 S891
[FMV/PFM]5LCY/[UNV1/UNV34] D 76 S903
[FMV/PFM]5LCY/[UNV1/UNV34] D 33
[FMV/PFM]5LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]7LCY/[UNV1/UNV34] 76
[FMV/PFM]7LCY/[UNV1/UNV34] 76 S891
[FMV/PFM]7LCY/[UNV1/UNV34] 76 S903
[FMV/PFM]7LCY/[UNV1/UNV34] 33
[FMV/PFM]7LCY/[UNV1/UNV34] 33 S903
[FMV/PFM]7LCY/[UNV1/UNV34] D 76
[FMV/PFM]7LCY/[UNV1/UNV34] D 76 S891
[FMV/PFM]7LCY/[UNV1/UNV34] D 76 S903
[FMV/PFM]7LCY/[UNV1/UNV34] D 33
[FMV/PFM]7LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]9LCY/[UNV1/UNV34] 76
[FMV/PFM]9LCY/[UNV1/UNV34] 76 S891
[FMV/PFM]9LCY/[UNV1/UNV34] 76 S903
[FMV/PFM]9LCY/[UNV1/UNV34] D 76
[FMV/PFM]9LCY/[UNV1/UNV34] D 76 S891
[FMV/PFM]9LCY/[UNV1/UNV34] D 76 S903

Part number*

[FMV/PFM]9LCY/[UNV1/UNV34] 33 S903
[FMV/PFM]9LCY/[UNV1/UNV34] D 76
[FMV/PFM]9LCY/[UNV1/UNV34] D 76 S891
[FMV/PFM]9LCY/[UNV1/UNV34] D 76 S903
[FMV/PFM]9LCY/[UNV1/UNV34] D 33
[FMV/PFM]9LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]11LCY/[UNV1/UNV34] 76
[FMV/PFM]11LCY/[UNV1/UNV34] 76 S903
[FMV/PFM]11LCY/[UNV1/UNV34] 33
[FMV/PFM]11LCY/[UNV1/UNV34] 33 S903
[FMV/PFM]11LCY/[UNV1/UNV34] D 33
[FMV/PFM]11LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]11LCY/[UNV1/UNV34] D 76
[FMV/PFM]11LCY/[UNV1/UNV34] D 76 S903
[FMV/PFM]13LCY/[UNV1/UNV34] 76
[FMV/PFM]13LCY/[UNV1/UNV34] 76 S903
[FMV/PFM]13LCY/[UNV1/UNV34] 33
[FMV/PFM]13LCY/[UNV1/UNV34] 33 S903

Part number*

[FMV/PFM]13LCY/[UNV1/UNV34] D 76
[FMV/PFM]13LCY/[UNV1/UNV34] D 76 S903
[FMV/PFM]13LCY/[UNV1/UNV34] D 33
[FMV/PFM]13LCY/[UNV1/UNV34] D 33 S903
[FMV/PFM]15LCY/[UNV1/UNV34] 76
[FMV/PFM]15LCY/[UNV1/UNV34] 76 S903
[FMV/PFM]15LCY/[UNV1/UNV34] 33
[FMV/PFM]15LCY/[UNV1/UNV34] 33 S903
[FMV/PFM]15LCY/[UNV1/UNV34] D 76
[FMV/PFM]15LCY/[UNV1/UNV34] D 76 S903
[FMV/PFM]15LCY/[UNV1/UNV34] D 33
[FMV/PFM]15LCY/[UNV1/UNV34] D 33 S903
[FMVA/PFMA]20LCY/[UNV1 /UNV34] 76
[FMVA/PFMA]20LCY/[UNV1/UNV34] 76 S903
[FMVA/PFMA]20LVY/[UNV1/UNV34] 76
[FMVA/PFMVA]25LCY/[UNV1/UNV34] 76

* For text within brackets, choose one or the other to complete part number (i.e. FMV or PVM).

Eaton's Crouse-Hinds **DLC** approved products

Industrial high bay (8L-64L)



IHB8L - 64L

Indoor

Part number*
IHB8L [/P1]/[UNV1/UNV34]
IHB8L [/P1]/[UNV1D/UNV34D]
IHB16L [/P1]/[UNV1/UNV34]
IHB16L [/P1]/[UNV1D/UNV34D]
IHB24L [/P1]/[UNV1/UNV34]
IHB24L [/P1]/[UNV1D/UNV34D]
IHB24L [UNV1/UNV34] S903
IHB24L P1/[UNV1/UNV34] S903

Part number*
IHB24L [UNV1/UNV34] S891
IHB24L P1/[UNV1/UNV34] S891
IHB24L R1/[UNV1/UNV34]
IHB24L P1R1/[UNV1/UNV34]
IHB24L R1/[UNV1/UNV34] S903
IHB24L P1R1/[UNV1/UNV34] S903
IHB24L R1/[UNV1/UNV34] S903D
IHB24L R1/[UNV1/UNV34] S891

Part number*
IHB24L P1R1/[UNV1/UNV34] S891
IHB32L [/P1]/[UNV1/UNV34]
IHB32L [/P1]/[UNV1D/UNV34D]
IHB48L [/P2]/[UNV1/UNV34]
IHB48L [/P2]/[UNV1D/UNV34D]
IHB64L [/P2]/[UNV1/UNV34]
IHB64L [/P2]/[UNV1D/UNV34D]

* For text within brackets, choose one or the other to complete part number (i.e. UNV1 or UNV34).

Pauluhn™ Apex (2 & 4 ft.)



25L



13L & 17L

Indoor

Part number*
APX13L [UNV1/UNV34] S903
APX13L [UNV1/UNV34] S903D
APX17L [UNV1/UNV34] S903

Part number*
APX17L [UNV1/UNV34] S903D
APX25L [UNV1/UNV34] S903
APX25L [UNV1/UNV34] S903D

* For text within brackets, choose one or the other to complete part number (i.e. UNV1 or UNV34).

Hazard•Gard® XPL and Pauluhn™ ZPL (4 ft.)



ZPL, XPL 4 ft.

Part number*
XPL/4/[UNV1/UNV34]
ZPL/4/[UNV1/UNV34]

* All finishes approved.

Hazard•Gard® EVLL (5L)



Part number*
EVLL5LC0/[UNV1/UNV34] /S812
EVLL5LC0/[UNV1/UNV34]

Part number*
nEVLL5LC0/[UNV1/UNV34] /S812
nEVLL5LC0/[UNV1/UNV34]

* For text within brackets, choose one or the other to complete part number (i.e. UNV1 or UNV34).